

# Specifications

## Eaton PRL1A3400X42CS

Eaton, interior circuit, prl1a no tfl 208y/120v  
cu bus

### General specifications

PRODUCT NAME	Eaton Pow-R-Stock PRL1A panelboard
CATALOG NUMBER	PRL1A3400X42CS
UPC	786689059491
PRODUCT LENGTH/DEPTH	46 in
PRODUCT HEIGHT	6 in
PRODUCT WIDTH	20 in
PRODUCT WEIGHT	40 lb
CERTIFICATIONS	Contact Manufacturer



### Product specifications

TYPE	Interior circuit
AMPERAGE RATING	400A
NUMBER OF CIRCUITS	42
PHASE	Single-phase

### Resources

MULTIMEDIA	<a href="#">Pow-R-Line Xpert family overview</a>
SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - PRL1A3400X42CS</a>

---

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**

---



**Eaton Corporation plc**

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights  
Reserved.

Eaton is a registered trademark.

All other trademarks are property of  
their respective owners.

Follow us on social media to get the latest  
product and support information.



# Specifications

## Eaton PRL1A3400X42CS

Eaton, interior circuit, prl1a no tfl 208y/120v  
cu bus

### General specifications

PRODUCT NAME	Eaton Pow-R-Stock PRL1A panelboard
CATALOG NUMBER	PRL1A3400X42CS
UPC	786689059491
PRODUCT LENGTH/DEPTH	46 in
PRODUCT HEIGHT	6 in
PRODUCT WIDTH	20 in
PRODUCT WEIGHT	40 lb
CERTIFICATIONS	Contact Manufacturer



### Product specifications

TYPE	Interior circuit
AMPERAGE RATING	400A
NUMBER OF CIRCUITS	42
PHASE	Single-phase

### Resources

MULTIMEDIA	<a href="#">Pow-R-Line Xpert family overview</a>
SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - PRL1A3400X42CS</a>

---

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**

---



**Eaton Corporation plc**

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights  
Reserved.

Eaton is a registered trademark.

All other trademarks are property of  
their respective owners.

Follow us on social media to get the latest  
product and support information.

