



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PS40MBR 400A 600V Male Cam Typ Plug Red

Pass & Seymour/Legrand

Catalog Number	PS40MBR
Manufacturer	Pass & Seymour/Legrand
Description	400A 600V, Male Cam Device Plug, Cable Size 2/0-4/0, Red
Weight per unit	0.7475 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

Features

amperage rating	400
Cord Type	Individual conductor, Type SC, SCE, SCT or W, 75°C, copper wire only
Poles	1
Voltage Rating	600
Wire Size	2/0 - 4/0

Dimensions and Weight

Size	6.875
------	-------

Descriptions

Description	400A 600V MALE CAM TYP PLUG RED
extra long description	P&S PS40MBR 400A 600V MALE CAM TYP
Long Description	400A 600V, Male Cam Device Plug, Cable Size 2/0-4/0, Red
Product Type	400A 600V Male Cam Typ Plug Red
Special Features	Thermoplastic elastomer housing for outstanding impact and chemical resistance, as well as an exceptional seal for maintaining NEMA Type 3R and 4 integrity. Non-conductive retaining screw helps to insure no contact with live parts, along with providing stability to the fully assembled product. Heavy-duty brass male and female contacts provide a superior and consistent means of conductivity. Heavy-duty hex set screws allow greater termination torque. Copper wire provides quality strain relief. Copper shim b

Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007308075
Manufacturers Part Number	PS40MBR
UPC	785007308075

Taxonomies, Classifications, and Categories

Category Description	Industrial cord connectors
Type	Cam-Type Series 16 In-Line Connector Male



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	10
Weight Per each	0.7475

Uses, Certifications, and Standards

Application	Commercial/Industrial
environmental conditions	Enclosure: NEMA Type 3R and 4;Flammability UL94 V2;Operating Temperature: Maximum continuous +75°C, minimum -40°C without impact
nema rating standard	Enclosure: NEMA Type 3R and 4 UL, cCSAus