



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## LB400DCG 4 LB FM5 Cond BC&G *Appleton/Oz Gedney*

Catalog Number	LB400DCG
Manufacturer	Appleton/Oz Gedney
Description	Emt Conduit Bodies, Aluminum Threaded For Rigid Conduit and Imc, Series: LB, Set Screw, Material: Conduit Body: Diecast, Copperfree Aluminum/Epoxy Powder Coat, Cover: Stamped Aluminum, Natural Finish, Gasket: Neoprene, UI Standard: 514A, Trade Size: 4
Weight per unit	10.0 (lbs/each)
Product Category	Alum

### Material, Color, and Finish

Finish	Epoxy Powder Coat
--------	-------------------

### Dimensions and Weight

Height	7.48
Hub Size	1-1/4
Length	8.450000000000000
Width	2.490000000000000

### Descriptions

Description	4 LB FM5 COND BC&G
extra long description	EGS LB400DCG 4 IN THD ALUM LB BDY C
Long Description	EMT Conduit Bodies, Aluminum Threaded for rigid conduit and IMC, Series: LB, Set Screw, Material: Conduit body: diecast, copperfree aluminum/epoxy powder coat, Cover: stamped aluminum, natural finish, Gasket: neoprene, UL Standard: 514A, Trade Size: 4
Product Type	4 In THD Alum LB Bdy CVR GSKT
Special Features	3-1/2 IN Trade Size, Type LB Aluminum Threaded Conduit Body, Maximum No. of Conductors 3 - #350MCM, Volume 308.00 IN <sup>3</sup> , For Use With Rigid and IMC Conduit, Furnished With Cover and Gasket

### Manufacturer Information

Brand	Appleton
GTIN	00687855001323
Manufacturers Part Number	LB400DCG
UPC	687855001323

### Taxonomies, Classifications, and Categories

Category Description	FORM 5 CONDULETS, COVERS, & GASKETS
Type	Conduit Body



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	10

## Uses, Certifications, and Standards

Application	Provides access to the interior of the raceway for wire pulling , splicing and maintenance, Allows connection of straight and branch conduit runs and 90 degree bends
standard	CSA Certified: 208044;CSA Standard: C22.2 No. 18.3;NEMA: FB-1;UL Listed: E53330;UL Standard: 514A