



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LC100DCG 1" Cond Body C/G *Appleton/Oz Gedney*

Catalog Number	LC100DCG
Manufacturer	Appleton/Oz Gedney
Description	Emt Conduit Bodies, Aluminum Threaded For Rigid Conduit and Imc, Material: Conduit Body: Diecast, Copperfree Aluminum/Epoxy Powder Coat, Cover: Stamped Aluminum, Natural Fi Nish, Gasket: Neoprene, Ul Standard: 514A, Trade Size: 1", Lengt
Weight per unit	0.6000 (lbs/each)
Product Category	Alum

Features

Material	Die Cast Aluminum
----------	-------------------

Material, Color, and Finish

Finish	Epoxy Powder Coat
--------	-------------------

Dimensions and Weight

Height	2.14
Hub Size	1
Length	6.44
Width	1.74

Descriptions

Description	1" COND BODY C/G
extra long description	EGS LC100DCG 1 IN THD ALUM LC BDY C
Long Description	EMT Conduit Bodies, Aluminum Threaded for Rigid Conduit and IMC, Material: Conduit body: diecast, copperfree aluminum/epoxy powder coat, Cover: stamped aluminum, natural fi nish, Gasket: neoprene, UL Standard: 514A, Trade Size: 1", Lengt
Product Type	1 In THD Alum LC Bdy CVR GSKT
Special Features	1 IN Trade Size, Type LC Aluminum Threaded Conduit Body, Maximum No. of Conductors 3 - #4 AWG, Volume 12.20 IN ³ , For Use With Rigid and IMC Conduit, Furnished With Stamped Aluminum Cover and Neoprene Gasket

Manufacturer Information

Brand	Appleton
GTIN	00687855000616
Manufacturers Part Number	LC100DCG
UPC	687855000616



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description FORM 5 CONDULETS, COVERS, & GASKETS
Type Conduit Body

Packaging

Carton 5
Package 20
Weight Per each 0.6

Uses, Certifications, and Standards

Application Provides access to the interior of the raceway for wire pulling ,
splicing and maintenance, Allows connection of straight and
branch conduit runs and 90 degree bends
standard CSA Certified: 208044;CSA Standard: C22.2 No. 18.3;NEMA:
FB-1;UL Listed: E53330;UL Standard: 514A