



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PSG480F24RM PWR Supply 3PHASE 24VDC 480W IP20 Term Metal

Eaton Corp

Catalog Number	PSG480F24RM
Manufacturer	Eaton Corp
Description	Eaton PSG Power Supply, Aluminum, 400-500 Vac, 47-63 HZ, Finger-Safe Terminals, 24 VDC Output, Three-Phase, 480W Output Power, -25°C-80°C Operating Temp
Weight per unit	3.0 (lbs/each)
Product Category	DC Power Supplies

Features

dimensions	7.0000 IN X 6.0000 IN X 7.0000 IN
media	Yes
Phase	Three-phase

Descriptions

Description	PWR SUPPLY 3PHASE 24VDC 480W IP20 TERM METAL
extra long description	ETN PSG480F24RM P.S. 3PH 24VDC 480W
Features	The PSG line of general purpose power supplies is used in a wide variety of industrial control applications. Applications include communication networks, sensors, PLCs and many other electrical systems. Each model is equipped with the options of a rugged metal or plastic housing, heavy-duty screw or finger-safe terminals and a variety of protection features. The PSG line offers the flexibility of operating with a universal input voltage of 100–240 Vac. It also provides system protection and continuous oper
Long Description	Eaton PSG power supply, Aluminum, 400-500 Vac, 47-63 Hz, Finger-safe terminals, 24 Vdc output, Three-phase, 480W output power, -25°C-80°C operating temp
Product Type	P.S. 3PH 24VDC 480W IP20 Term Metal

Manufacturer Information

Brand	Eaton
GTIN	00786685683607
Manufacturers Part Number	PSG480F24RM
UPC	786685683607

Taxonomies, Classifications, and Categories

Category Description	POWER SUPPLIES
Type	General purpose power supply

Packaging

Carton	1
Weight Per each	3



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels and OEMs
Frequency Rating	47-63 Hz
standard	UL 508, CSA Std. C22.2, IEC Rated, EN Listed, RoHS Compliant, CE Marked