








# LED replacement lamps

## A-Line Lamps

Bulb Shape	Base Type	Watts	Order Code	Description	Volts	Case Qty**	MOL (In)	Lumens Initial	CBCP	Initial Color Temp	CRI	Wattage Replacement	*Rated Life L70 (Hrs)	Dimmable	ENERGY STAR® Status	#Location Rating	Additional Information	
<b>A-15</b>																		
	MED	4	34038	LED4DA15-W3/827	120	6	3.5	300		2700	80	40W	15,000	Yes		Damp	White	
			34051	LED4DA15-C3/827	120	6	3.5	300		2700	80	40W	15,000	Yes		Damp	Clear	
	MED	4.5	14644	LED4.5DA15-C/827	120	6	3.5	300		2700	80	40W	15,000	Yes		Damp	Clear	
			23708	LED4.5DA15-W5KTP	120	3	3.5	350		5000	80	40W	15,000	Yes		Damp	White	
			23724	LED4.5DA15-C5KTP	120	3	3.5	350		5000	80	40W	15,000	Yes		Damp	Clear	
<b>A-19</b>																		
	MED	7	14063	LED7DAV3/827W	120	6	4.6	470		2700	80	40W	25,000	Yes		Damp	White, Semi-Omni	
			95928	LED7DAV3/5K	120	6	4.6	500		5000	80	40W	25,000	Yes		Damp	White, Semi-Omni	
			11332	LED7DA19/827	120	6	4.4	450		2700	80	40W	25,000	Yes	★	Damp	White, Omnidirectional	
			71208	LED7DA19/830	120	6	4.4	450		3000	80	40W	25,000	Yes	★	Damp	White, Omnidirectional	
			34238	LED7DA19/824	120	6	4.44	450		2400	80	40W	25000	Yes		Damp	White	
	10.5	13791	LED11DAV3/827W	120	6	4.6	800		2700	80	60W	15,000	Yes		Damp	White, Semi-Omni		
			95927	LED11DAV3/5K	120	6	4.4	850		5000	80	60W	15,000	Yes		Damp	White, Semi-Omni	
			11328	LED11DA19/827	120	6	4.4	800		2700	80	60W	25,000	Yes	★	Damp	White, Omnidirectional	
			71209	LED11DA19/830	120	6	4.4	800		3000	80	60W	25,000	Yes	★	Damp	White, Omnidirectional	
			29268	LED11DA19/824	120	6	4.44	800		2400	80	60W	25,000	-		Damp	White, Omnidirectional	
GU24	74357	LED11DA19827GU24	120	6	5.43	800		2700	80	60W	25,000	-	★	Damp	White, Omnidirectional			
<b>A-Line reveal®</b>																		
	MED	7	63178	LED7DA19RVLESTP	120	3	4.43	450		2700	84	40W	25,000	Yes		Damp	White, Omnidirectional	
			11	63180	LED11DA19RVLESTP	120	3	4.43	800		2700	84	60W	25,000	Yes		Damp	White, Omnidirectional
			14	92284	LED14DA21RVL/TP	120	3	5.28	1100		2700	85	75W	25,000	Yes		Damp	White, Omnidirectional
<b>A-21</b>																		
	MED	12	73384	LED12A21/830FE	120	6	5.31	1100		3000	80	75W	25,000	Yes		Damp	White, Enclosed, Omni	
			73404	LED12DA21/850FE	120	6	5.31	1100		5000	80	75W	25,000	Yes		Damp	White, Enclosed, Omni	
			13	12422	LED13DA212/827	120	6	5.28	1100		2700	80	75W	25,000	Yes	★	Damp	White, Omnidirectional
			14	94936	LED14DA21/827W	120	6	5.3	1100		2700	80	75W	15,000	Yes		Damp	White, Semi-Omni
			16	12349	LED16DA212/827	120	6	5.28	1600		2700	80	100W	25,000	Yes	★	Damp	White, Omnidirectional
	GU24	16	92498	LED16DA21827GU24	120	6	5.43	1600		2700	80	100W	25,000	Yes	★	Damp	White	
			73376	LED16A30/100/827	120	6	5.31	400/1600/1050		2700	80	30/70/100	25,000	-	★	Damp	3-Way	
			92118	LED16A30/100/5KB	120	3	5.31	400/1600/1050		5000	80	30/70/100	25,000	-	★		White, 3-Way	
			17	16113	LED17DA21/827	120	6	5.3	1600		2700	78	100W	15,000	Yes		Damp	White, Semi-Omni
			22	73378	LED22A50/150/827	150	6	5.31	700/2155/1600		2700	80	50/100/150	25,000	-		Damp	3-Way
			92120	LED22A50/150/5KB	120	3	5.31	700/2155/1600		5000	80	50/100/150	25,000	-			White, 3-Way	

## LED Bright Stik™

Bulb Shape	Base Type	Watts	Order Code	Description	Volts	Case Qty**	MOL (In)	Lumens Initial	CBCP	Initial Color Temp	CRI	Wattage Replacement	*Rated Life L70 (Hrs)	Dimmable	ENERGY STAR® Status	#Location Rating	Additional Information	
<b>LED Bright Stik™</b>																		
	MED	10	28089	LED10LS3/828	120	48	4.45	760		2840	80	60W	15,000	-		Indoor	Case = 16 3-packs	
			32273	LED10LS3/850	120	48	4.45	760		5000	80	60W	15,000	-		Indoor	Case = 16 3-packs	
	MED	16	35523	LED16LS2/828	120	32	5.31	1520		2850	88	100W	15,000	-		Indoor	Case = 16 2-packs	
			35524	LED16LS2/850	120	32	5.31	1520		2850	88	100W	15,000	-		Indoor	Case = 16 2-packs	

### Updated / New Product

Information provided is subject to change without notice. Please verify all details with GE. All values are design or typical values when measured under laboratory conditions, and GE makes no warranty or guarantee, expressed or implied, that such performance will be obtained under end-use conditions.

\* The life rating is based on the hours of operation the lamp will provide before reaching 70% of its original rating (L70)

\*\* Minimum order quantity = 6

★ ENERGY STAR® status: ENERGY STAR® certified. Lamps without a ★ are not ENERGY STAR® certified.

# UL 1993 Environmental Requirements for LED LAMPS

Location, damp - Exterior or interior location that is normally or periodically subject to condensation of moisture in, on, or adjacent to, electrical equipment, and includes partially protected locations.

Location, dry - Location not normally subject to dampness, may include a location subject to temporary dampness, i.e., building under construction, provided ventilation is adequate to prevent an accumulation of moisture.







Location, wet - Location in which water or other liquid can drip, splash, or flow on or against electrical equipment.

Notes: 1) Product descriptions ending in "/TP" indicate a carded blister or clamshell package nested in a tray for shelf display. Cards also designed for hook display. 2) LED A19 Locking device works on PC: 85791, 85792, 89898, 62182, 89899 and 89900


Get more information at  
[GELighting.com/ThinkLED](http://GELighting.com/ThinkLED)

# LED replacement lamps

## A-Line Lamps

Bulb Shape	Base Type	Watts	Order Code	Description	Volts	Case Qty**	MOL (In)	Lumens Initial	CBCP	Initial Color Temp	CRI	Wattage Replacement	*Rated Life L70 (Hrs)	Dimmable	ENERGY STAR® Status	#Location Rating	Additional Information			
<b>A-15</b>																				
	MED	4	34038	LED4DA15-W3/827	120	6	3.5	300		2700	80	40W	15,000	Yes		Damp	White			
			34051	LED4DA15-C3/827	120	6	3.5	300		2700	80	40W	15,000	Yes		Damp	Clear			
	MED	4.5	14644	LED4.5DA15-C/827	120	6	3.5	300		2700	80	40W	15,000	Yes		Damp	Clear			
			23708	LED4.5DA15-W5KTP	120	3	3.5	350		5000	80	40W	15,000	Yes		Damp	White			
			23724	LED4.5DA15-C5KTP	120	3	3.5	350		5000	80	40W	15,000	Yes		Damp	Clear			
<b>A-19</b>																				
	MED	7	14063	LED7DAV3/827W	120	6	4.6	470		2700	80	40W	25,000	Yes		Damp	White, Semi-Omni			
			95928	LED7DAV3/5K	120	6	4.6	500		5000	80	40W	25,000	Yes		Damp	White, Semi-Omni			
			11332	LED7DA19/827	120	6	4.4	450		2700	80	40W	25,000	Yes	★	Damp	White, Omnidirectional			
			71208	LED7DA19/830	120	6	4.4	450		3000	80	40W	25,000	Yes	★	Damp	White, Omnidirectional			
			34238	LED7DA19/824	120	6	4.44	450		2400	80	40W	25000	Yes		Damp	White			
	10.5	13791	LED11DAV3/827W	120	6	4.6	800		2700	80	60W	15,000	Yes		Damp	White, Semi-Omni				
			95927	LED11DAV3/5K	120	6	4.4	850		5000	80	60W	15,000	Yes		Damp	White, Semi-Omni			
			11328	LED11DA19/827	120	6	4.4	800		2700	80	60W	25,000	Yes	★	Damp	White, Omnidirectional			
			71209	LED11DA19/830	120	6	4.4	800		3000	80	60W	25,000	Yes	★	Damp	White, Omnidirectional			
			29268	LED11DA19/824	120	6	4.44	800		2400	80	60W	25,000	-		Damp	White, Omnidirectional			
	GU24	74357	LED11DA19827GU24	120	6	5.43	800		2700	80	60W	25,000	-	★	Damp	White, Omnidirectional				
<b>A-Line reveal®</b>																				
	MED	7	63178	LED7DA19RVLESTP	120	3	4.43	450		2700	84	40W	25,000	Yes		Damp	White, Omnidirectional			
			11	63180	LED11DA19RVLESTP	120	3	4.43	800		2700	84	60W	25,000	Yes		Damp	White, Omnidirectional		
			14	92284	LED14DA21RVL/TP	120	3	5.28	1100		2700	85	75W	25,000	Yes		Damp	White, Omnidirectional		
<b>A-21</b>																				
	MED	12	73384	LED12A21/830FE	120	6	5.31	1100		3000	80	75W	25,000	Yes		Damp	White, Enclosed, Omni			
			73404	LED12DA21/850FE	120	6	5.31	1100		5000	80	75W	25,000	Yes		Damp	White, Enclosed, Omni			
			13	12422	LED13DA212/827	120	6	5.28	1100		2700	80	75W	25,000	Yes	★	Damp	White, Omnidirectional		
			14	94936	LED14DA21/827W	120	6	5.3	1100		2700	80	75W	15,000	Yes		Damp	White, Semi-Omni		
			16	12349	LED16DA212/827	120	6	5.28	1600		2700	80	100W	25,000	Yes	★	Damp	White, Omnidirectional		
				12399	LED16DA212/830	120	6	5.3	1600		3000	80	100W	25,000	Yes	★	Damp	White, Omnidirectional		
				92498	LED16DA21827GU24	120	6	5.43	1600		2700	80	100W	25,000	Yes	★	Damp	White		
				GU24	16	73376	LED16A30/100/827	120	6	5.31	400/1600/1050		2700	80	30/70/100	25,000	-	★	Damp	3-Way
						92118	LED16A30/100/5KB	120	3	5.31	400/1600/1050		5000	80	30/70/100	25,000	-	★		White, 3-Way
						17	16113	LED17DA21/827	120	6	5.3	1600		2700	78	100W	15,000	Yes		Damp
	MED	22	73378	LED22A50/150/827	150	6	5.31	700/2155/1600		2700	80	50/100/150	25,000	-		Damp	3-Way			
			92120	LED22A50/150/5KB	120	3	5.31	700/2155/1600		5000	80	50/100/150	25,000	-			White, 3-Way			

## LED Bright Stik™

Bulb Shape	Base Type	Watts	Order Code	Description	Volts	Case Qty**	MOL (In)	Lumens Initial	CBCP	Initial Color Temp	CRI	Wattage Replacement	*Rated Life L70 (Hrs)	Dimmable	ENERGY STAR® Status	#Location Rating	Additional Information	
<b>LED Bright Stik™</b>																		
	MED	10	28089	LED10LS3/828	120	48	4.45	760		2840	80	60W	15,000	-		Indoor	Case = 16 3-packs	
			32273	LED10LS3/850	120	48	4.45	760		5000	80	60W	15,000	-		Indoor	Case = 16 3-packs	
	MED	16	35523	LED16LS2/828	120	32	5.31	1520		2850	88	100W	15,000	-		Indoor	Case = 16 2-packs	
			35524	LED16LS2/850	120	32	5.31	1520		2850	88	100W	15,000	-		Indoor	Case = 16 2-packs	

### Updated / New Product

Information provided is subject to change without notice. Please verify all details with GE. All values are design or typical values when measured under laboratory conditions, and GE makes no warranty or guarantee, expressed or implied, that such performance will be obtained under end-use conditions.

\* The life rating is based on the hours of operation the lamp will provide before reaching 70% of its original rating (L70)

\*\* Minimum order quantity = 6

★ ENERGY STAR® status: ENERGY STAR® certified. Lamps without a ★ are not ENERGY STAR® certified.

# UL 1993 Environmental Requirements for LED LAMPS

Location, damp - Exterior or interior location that is normally or periodically subject to condensation of moisture in, on, or adjacent to, electrical equipment, and includes partially protected locations.

Location, dry - Location not normally subject to dampness, may include a location subject to temporary dampness, i.e., building under construction, provided ventilation is adequate to prevent an accumulation of moisture.

Location, wet - Location in which water or other liquid can drip, splash, or flow on or against electrical equipment.

Notes: 1) Product descriptions ending in "/TP" indicate a carded blister or clamshell package nested in a tray for shelf display. Cards also designed for hook display. 2) LED A19 Locking device works on PC: 85791, 85792, 89898, 62182, 89899 and 89900

Get more information at  
[GELighting.com/ThinkLED](http://GELighting.com/ThinkLED)