





LED replacement lamps

Reflector Lamps

Bulb Shape	Base Type	Watts	Order Code	Description	Volts	Case Qty**	MOL (In)	Lumens Initial	CBCP	Initial Color Temp	CRI	Wattage Replacement	*Rated Life L70 (Hrs)	Dimmable	ENERGY STAR® Status	#Location Rating	Additional Information	
R20																		
	MED	7	13829	LED7DRS20F827	120	6	3.6	470		2700	80		25,000	Yes		Damp	White	
			14065	LED7DRS20F830	120	6	3.6	470		3000	80		25,000	Yes		Damp	White	
BR30																		
	MED	10	68160	LED10DR303/827W	120	6	5.4	700		2700	80	65W	25,000	Yes	★	Damp	Frosted, White body	
			68161	LED10DR303/830W	120	6	5.4	700		3000	80	65W	25,000	Yes	★	Damp	Frosted, White body	
			89942	LED10DR303/5K/TP	120	3	5.37	700		5000	80	65W	25,000	Yes	★	Damp	Frosted, White body	
BR30 reveal®																		
		10	92470	LED10DR303RVL	120	3	5.37	650		2700	90	65W	25,000	Yes	★	Damp	Frosted, White body	
BR40																		
	MED	13	64176	LED13DBR40/827	120	6	6.3	1070		2700	80	85W	25,000	Yes	★	Damp	Frosted, White body	
			14708	LED13DBR40/830	120	6	6.3	1070		3000	80	85W	25,000	Yes	★	Damp	Frosted, White body	
			20445	LED13BR40/5K/TP	120	3	6.34	1070		5000	80	85W	25,000	Yes	★	Damp	Frosted, White body	

Directional Lamps (MR16 - GU10)

Bulb Shape	Base Type	Watts	Order Code	Description	Volts	Case Qty**	MOL (In)	Lumens Initial	CBCP	Initial Color Temp	CRI	Wattage Replacement	*Rated Life L70 (Hrs)	Dimmable	ENERGY STAR® Status	#Location Rating	Additional Information			
12 Volt AC/DC MR16																				
	GU5.3	7	93412	LED7DMR16S830/15	12	6	2.3	460	3800	3000	80	35W	25,000	Yes	★	Dry	Accent, 15° beam, Silver			
			69920	LED7DMR16D830/25	12	6	1.9	390	1900	3000	83	35W	25,000	Yes		Dry	Accent, 25° beam, Silver			
			69925	LED7DMR16D840/15	12	6	1.9	430	4000	4000	87	35W	25,000	Yes		Dry	Accent, 15° beam, Silver			
			93431	LED7DMR16S827/15	12	6	1.97	440	3700	2700	80	35W	25,000	Yes	★	Dry	Accent, 15° beam, Silver			
			93433	LED7DMR16S840/15	12	6	1.97	490	4200	4000	80	35W	25,000	Yes	★	Dry	Accent, 15° beam, Silver			
			39351	LED7DMRX16830/35	12	6	1.97	420	1100	3000	82	35W	25,000	Yes	★	Dry	Accent, 35° beam, White			
			69949	LED7XDMR16S83025	12	6	1.9	500	2500	3000	82	50W	25,000	Yes	★	Dry	Accent, 25° beam, Silver			
			69950	LED7XDMR16S83035	12	6	1.9	500	1500	3000	82	50W	25,000	Yes	★	Dry	Accent, 35° beam, Silver			
			69951	LED7XDMR16S82725	12	6	1.9	480	2400	2700	80	50W	25,000	Yes	★	Dry	Accent, 25° beam, Silver			
			69952	LED7XDMR16S82735	12	6	1.9	480	1400	2700	80	50W	25,000	Yes	★	Dry	Accent, 35° beam, Silver			
				GU5.3	7	35196	LED7XDMRX1683025	12	6	2.2	500	1350	3000	80	50W	25,000	Yes		Dry	Accent, 35° beam, White
						35206	LED7XDMRX1682725	12	6	2.2	480	2350	2700	80	50W	25,000	Yes		Dry	Accent, 25° beam, White
39360	LED7DMRX16827/25	12				6	2.2	400	1800	2700	80	35W	25,000	Yes	★	Dry	Accent, 25° beam, White			
39405	LED7DMRX16827/35	12				6	2.2	400	1000	2700	80	35W	25,000	Yes	★	Dry	Accent, 35° beam, White			
39408	LED7DMRX16840/25	12				6	2.2	460	2100	4000	83	35W	25,000	Yes	★	Dry	Accent, 25° beam, White			
	GU5.3	6	39468	LED6DMR16-V82735	12	6	1.8	430	1150	2700	80	35W	25,000	Yes		Dry	Accent, 35° beam, White			
			39438	LED6DMR16-V83035	12	6	1.8	460	1200	3000	80	35W	25,000	Yes		Dry	Accent, 35° beam, White			
			39472	LED6DMR16-V84035	12	6	1.8	500	1300	4000	80	35W	25,000	Yes		Dry	Accent, 35° beam, White			
	7		39473	LED7XDMR16-V8325	12	6	1.88	550	2400	3000	80	50W	25,000	Yes		Dry	Accent, 25° beam, White			
			39483	LED7XDMR16-V8335	12	6	1.88	550	1400	3000	80	50W	25,000	Yes		Dry	Accent, 35° beam, White			
			39542	LED7XDMR16-V2725	12	6	1.88	530	2400	2700	80	50W	25,000	Yes		Dry	Accent, 25° beam, White			
			39567	LED7XDMR16-V2735	12	6	1.88	530	1400	2700	80	50W	25,000	Yes		Dry	Accent, 35° beam, White			
120 Volt GU10																				
	GU10	4	89020	LED4D/GU10/NFLTP	120	3	2.3	250	720	3000	80	35W	25,000	Yes	★	Dry	Accent, 35° beam, White			
			6	26346	LED6D/GU10/NFL/TP	120	3	2.3	380	1100	3000	80	50W	25,000	Yes	★	Dry	Accent, 35° beam, White		

Updated / New Product

Information provided is subject to change without notice. Please verify all details with GE. All values are design or typical values when measured under laboratory conditions, and GE makes no warranty or guarantee, expressed or implied, that such performance will be obtained under end-use conditions.

* The life rating is based on the hours of operation the lamp will provide before reaching 70% of its original rating (L70)

** Minimum order quantity = 6

★ ENERGY STAR® status: ENERGY STAR® certified. Lamps without a "★" are not ENERGY STAR® certified.

UL 1993 Environmental Requirements for LED LAMPS

Location, damp - Exterior or interior location that is normally or periodically subject to condensation of moisture in, on, or adjacent to, electrical equipment, and includes partially protected locations.

Location, dry - Location not normally subject to dampness, may include a location subject to temporary dampness, i.e., building under construction, provided ventilation is adequate to prevent an accumulation of moisture.

Location, wet - Location in which water or other liquid can drip, splash, or flow on or against electrical equipment.

Notes: 1) Product descriptions ending in "/TP" indicate a carded blister or clamshell package nested in a tray for shelf display. Cards also designed for hook display. 2) LED A19 Locking device works on PC: 85791, 85792, 89898, 62182, 89899 and 89900





Get more information at
GELighting.com/ThinkLED

LED replacement lamps

Reflector Lamps

Bulb Shape	Base Type	Watts	Order Code	Description	Volts	Case Qty**	MOL (In)	Lumens Initial	CBCP	Initial Color Temp	CRI	Wattage Replacement	*Rated Life L70 (Hrs)	Dimmable	ENERGY STAR® Status	#Location Rating	Additional Information	
R20																		
	MED	7	13829	LED7DRS20F827	120	6	3.6	470		2700	80		25,000	Yes		Damp	White	
			14065	LED7DRS20F830	120	6	3.6	470		3000	80		25,000	Yes		Damp	White	
BR30																		
	MED	10	68160	LED10DR303/827W	120	6	5.4	700		2700	80	65W	25,000	Yes	★	Damp	Frosted, White body	
			68161	LED10DR303/830W	120	6	5.4	700		3000	80	65W	25,000	Yes	★	Damp	Frosted, White body	
			89942	LED10DR303/5K/TP	120	3	5.37	700		5000	80	65W	25,000	Yes	★	Damp	Frosted, White body	
BR30 reveal®																		
		10	92470	LED10DR303RVL	120	3	5.37	650		2700	90	65W	25,000	Yes	★	Damp	Frosted, White body	
BR40																		
	MED	13	64176	LED13DBR40/827	120	6	6.3	1070		2700	80	85W	25,000	Yes	★	Damp	Frosted, White body	
			14708	LED13DBR40/830	120	6	6.3	1070		3000	80	85W	25,000	Yes	★	Damp	Frosted, White body	
			20445	LED13BR40/5K/TP	120	3	6.34	1070		5000	80	85W	25,000	Yes	★	Damp	Frosted, White body	

Directional Lamps (MR16 - GU10)

Bulb Shape	Base Type	Watts	Order Code	Description	Volts	Case Qty**	MOL (In)	Lumens Initial	CBCP	Initial Color Temp	CRI	Wattage Replacement	*Rated Life L70 (Hrs)	Dimmable	ENERGY STAR® Status	#Location Rating	Additional Information				
12 Volt AC/DC MR16																					
	GU5.3	7	93412	LED7DMR16S830/15	12	6	2.3	460	3800	3000	80	35W	25,000	Yes	★	Dry	Accent, 15° beam, Silver				
			69920	LED7DMR16D830/25	12	6	1.9	390	1900	3000	83	35W	25,000	Yes		Dry	Accent, 25° beam, Silver				
			69925	LED7DMR16D840/15	12	6	1.9	430	4000	4000	87	35W	25,000	Yes		Dry	Accent, 15° beam, Silver				
			93431	LED7DMR16S827/15	12	6	1.97	440	3700	2700	80	35W	25,000	Yes	★	Dry	Accent, 15° beam, Silver				
			93433	LED7DMR16S840/15	12	6	1.97	490	4200	4000	80	35W	25,000	Yes	★	Dry	Accent, 15° beam, Silver				
			39351	LED7DMRX16830/35	12	6	1.97	420	1100	3000	82	35W	25,000	Yes	★	Dry	Accent, 35° beam, White				
			69949	LED7XDMR16S83025	12	6	1.9	500	2500	3000	82	50W	25,000	Yes	★	Dry	Accent, 25° beam, Silver				
			69950	LED7XDMR16S83035	12	6	1.9	500	1500	3000	82	50W	25,000	Yes	★	Dry	Accent, 35° beam, Silver				
			69951	LED7XDMR16S82725	12	6	1.9	480	2400	2700	80	50W	25,000	Yes	★	Dry	Accent, 25° beam, Silver				
			69952	LED7XDMR16S82735	12	6	1.9	480	1400	2700	80	50W	25,000	Yes	★	Dry	Accent, 35° beam, Silver				
				GU5.3	7	35196	LED7XDMRX1683025	12	6	2.2	500	1350	3000	80	50W	25,000	Yes		Dry	Accent, 35° beam, White	
						35206	LED7XDMRX1682725	12	6	2.2	480	2350	2700	80	50W	25,000	Yes		Dry	Accent, 25° beam, White	
39360	LED7DMRX16827/25	12				6	2.2	400	1800	2700	80	35W	25,000	Yes	★	Dry	Accent, 25° beam, White				
39405	LED7DMRX16827/35	12				6	2.2	400	1000	2700	80	35W	25,000	Yes	★	Dry	Accent, 35° beam, White				
39408	LED7DMRX16840/25	12				6	2.2	460	2100	4000	83	35W	25,000	Yes	★	Dry	Accent, 25° beam, White				
	GU5.3	6	39468	LED6DMR16-V82735	12	6	1.8	430	1150	2700	80	35W	25,000	Yes		Dry	Accent, 35° beam, White				
			39438	LED6DMR16-V83035	12	6	1.8	460	1200	3000	80	35W	25,000	Yes		Dry	Accent, 35° beam, White				
			39472	LED6DMR16-V84035	12	6	1.8	500	1300	4000	80	35W	25,000	Yes		Dry	Accent, 35° beam, White				
			7	39473	LED7XDMR16-V8325	12	6	1.88	550	2400	3000	80	50W	25,000	Yes		Dry	Accent, 25° beam, White			
				39483	LED7XDMR16-V8335	12	6	1.88	550	1400	3000	80	50W	25,000	Yes		Dry	Accent, 35° beam, White			
			39542	LED7XDMR16-V2725	12	6	1.88	530	2400	2700	80	50W	25,000	Yes		Dry	Accent, 25° beam, White				
			39567	LED7XDMR16-V2735	12	6	1.88	530	1400	2700	80	50W	25,000	Yes		Dry	Accent, 35° beam, White				
			120 Volt GU10																		
				GU10	4	89020	LED4D/GU10/NFLTP	120	3	2.3	250	720	3000	80	35W	25,000	Yes	★	Dry	Accent, 35° beam, White	
						6	26346	LED6D/GU10/NFL/TP	120	3	2.3	380	1100	3000	80	50W	25,000	Yes	★	Dry	Accent, 35° beam, White

Updated / New Product

Information provided is subject to change without notice. Please verify all details with GE. All values are design or typical values when measured under laboratory conditions, and GE makes no warranty or guarantee, expressed or implied, that such performance will be obtained under end-use conditions.

* The life rating is based on the hours of operation the lamp will provide before reaching 70% of its original rating (L70)

** Minimum order quantity = 6

★ ENERGY STAR® status: ENERGY STAR® certified. Lamps without a "★" are not ENERGY STAR® certified.

UL 1993 Environmental Requirements for LED LAMPS

Location, damp - Exterior or interior location that is normally or periodically subject to condensation of moisture in, on, or adjacent to, electrical equipment, and includes partially protected locations.

Location, dry - Location not normally subject to dampness, may include a location subject to temporary dampness, i.e., building under construction, provided ventilation is adequate to prevent an accumulation of moisture.

Location, wet - Location in which water or other liquid can drip, splash, or flow on or against electrical equipment.

Notes: 1) Product descriptions ending in "/TP" indicate a carded blister or clamshell package nested in a tray for shelf display. Cards also designed for hook display. 2) LED A19 Locking device works on PC: 85791, 85792, 89898, 62182, 89899 and 89900

Get more information at
GELighting.com/ThinkLED