

# Specifications

## Eaton QBGFT2050

Eaton QB GFCI circuit breaker, Ground fault circuit breaker, 50A, 10 kAIC, Two-pole, 120/240V, Common trip, 5 mA Trip sensitivity, #8-6 Cu, #6-4 Al, QBGF



Photo is representative

### General specifications

PRODUCT NAME	Eaton QB GFCI circuit breaker
CATALOG NUMBER	QBGFT2050
UPC	786676026697
PRODUCT LENGTH/DEPTH	6.5 in
PRODUCT HEIGHT	2 in
PRODUCT WIDTH	3.5 in
PRODUCT WEIGHT	0.8 lb
WARRANTY	1 year
CERTIFICATIONS	UL 489
CATALOG NOTES	HACR rated



### Physical Attributes

CIRCUIT BREAKER TYPE QBGF

### Performance Ratings

AMPERAGE RATING 50 A

<b>MOUNTING METHOD</b>	Bolt-on
<b>NUMBER OF POLES</b>	Two-pole
<b>TYPE</b>	Ground fault circuit breaker
<b>WIRE SIZE</b>	#6-4 Al #8-6 Cu

<b>INTERRUPT RATING</b>	10 kAIC
<b>TRIP TYPE</b>	Common trip
<b>TRIP RATING</b>	5 mA trip sensitivity
<b>VOLTAGE RATING</b>	120/240 V

## Miscellaneous

<b>SPECIAL FEATURES</b>	5 mA Trip Sensitivity
-------------------------	-----------------------

## Resources

<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Eaton Specification Sheet - QBGFT2050</a>
--------------------------------------	---

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



# Specifications

## Eaton QBGFT2050

Eaton QB GFCI circuit breaker, Ground fault circuit breaker, 50A, 10 kAIC, Two-pole, 120/240V, Common trip, 5 mA Trip sensitivity, #8-6 Cu, #6-4 Al, QBGF



Photo is representative

### General specifications

PRODUCT NAME	Eaton QB GFCI circuit breaker
CATALOG NUMBER	QBGFT2050
UPC	786676026697
PRODUCT LENGTH/DEPTH	6.5 in
PRODUCT HEIGHT	2 in
PRODUCT WIDTH	3.5 in
PRODUCT WEIGHT	0.8 lb
WARRANTY	1 year
CERTIFICATIONS	UL 489
CATALOG NOTES	HACR rated



### Physical Attributes

CIRCUIT BREAKER TYPE QBGF

### Performance Ratings

AMPERAGE RATING 50 A

<b>MOUNTING METHOD</b>	Bolt-on
<b>NUMBER OF POLES</b>	Two-pole
<b>TYPE</b>	Ground fault circuit breaker
<b>WIRE SIZE</b>	#6-4 Al #8-6 Cu

<b>INTERRUPT RATING</b>	10 kAIC
<b>TRIP TYPE</b>	Common trip
<b>TRIP RATING</b>	5 mA trip sensitivity
<b>VOLTAGE RATING</b>	120/240 V

## Miscellaneous

<b>SPECIAL FEATURES</b>	5 mA Trip Sensitivity
-------------------------	-----------------------

## Resources

<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Eaton Specification Sheet - QBGFT2050</a>
--------------------------------------	---

<b>PROJECT NAME:</b>
----------------------

<b>PROJECT NUMBER:</b>
------------------------

<b>PREPARED BY:</b>
---------------------

<b>DATE:</b>
--------------



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

