



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



ROS20 #8-2/0 Awg Direct Burial "Cold Roll-On" Splice

Nsi Industries

| | |
|------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Catalog Number | ROS20 |
| Manufacturer | Nsi Industries |
| Description | Easy-Splice Roll On, Black Insulation Color, Sealing Strip, -40 °C Operating Temperature, +90 °C Operating Temperature, 5 In (Connector);8 In (Sleeve) Overall Length, 1000 V, 0.17 LB |
| Weight per unit | 0.1700 (lbs/each) |
| Product Category | Splicing & Terminating Kits |

Features

| | |
|----------------|----------------|
| Cable Size | 8-2/0 AWG |
| Cable Type | Class A-B |
| insulation | EPDM Elastomer |
| Material | EPDM RUBBER |
| Voltage Rating | 1000 V |
| Warranty | 1 YEAR |

Material, Color, and Finish

| | |
|-------|-------|
| Color | Black |
|-------|-------|

Descriptions

| | |
|------------------------|----------------------------------------------------------------------|
| Description | #8-2/0 AWG DIRECT BURIAL "COLD ROLL-ON" SPLICE |
| extra long description | NSI ROS-2/0 Easy-Splice Roll On 2/0 |
| Special Features | Easy Roll-On Way To Insulate And Seal Cable - Made Of EPDM Elastomer |

Manufacturer Information

| | |
|------|----------------|
| GTIN | 00662381123350 |
| UPC | 662381123350 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---------------------|
| Category Description | SPLICE KITS |
| Type | Roll-On Splice Kits |

Packaging

| | |
|-----------------|------|
| Carton | 6 |
| Weight Per each | 0.17 |

Uses, Certifications, and Standards

| | |
|--------------------------------|------------------------------------------------------|
| Application | Splicing Wire |
| Operating Temperature standard | -40 C To 90 C ANSI C119.1-1986 Qualified, UL 486D |