


COOPER LIGHTING - LUMARK®



CL/CS CANOPY LIGHT

1 0 0 - 4 0 0 W

High Pressure Sodium
Pulse Start Metal Halide
Metal Halide


CANOPY LIGHT
AREA/SITE LIGHT

- CL housing is constructed of heavy-gauge aluminum with welded corners providing good heat dissipation. CS housing is constructed of durable steel welded construction
- Weather- and abrasion-resistant white polyester powder coat finish
- Fully gasketed door frame seals out contaminants
- High power factor ballast with class H insulation. CL construction is listed for 40°C ambient environments. CS construction is listed for 25°C ambient environments
- Optical system features an injection-molded prismatic lens with internal prisms and white highly reflective internal surface
- Hinged door provides easy access for maintenance and relamping and door can be removed to simplify installation
- Approximate net weight: 44 lbs. (20 kgs.)

DESCRIPTION

The Lumark Canopy Light combines lasting durability and excellent photometrics. The CL housing consist of a heavy-gauge aluminum construction with welded corners and finished in a polyester powder paint. The CS housing is a durable welded steel construction finished in a polyester powder paint. Both are U.L. listed and CSA certified for wet locations.

DIMENSIONS



ORDERING INFORMATION

SAMPLE NUMBER: MHCL-400-MT-Q

Lamp Type	Series	Lamp Wattage ⁴	Voltage ⁶	Options & Accessories (See Below)
HP=High Pressure Sodium	CL=Canopy Light (Aluminum Housing) ²	100=100W	120V	
MH=Metal Halide	CS=Canopy Light (Steel Housing) ³	150=150W	208V	
MP=Pulse Start MH (CWA) ¹		175=175W	240V	
		200=200W	277V	
		250=250W	347V	
		320=320W ⁵	480V	
		350=350W ⁵	MT=Multi-Tap ⁷	
		400=400W ²	TT=Triple-Tap ⁸	

Options (add as suffix) *

- Q=Quartz Restrike DC Bayonet Base (Hot strike only)
- EM=Quartz Restrike with "Delay Relay"-Housing Mounted (Strikes at cold start)
- F1=Single Fuse (120, 277 or 347V)
- F2=Double Fused (208, 240 or 480V)
- C73=Flat Prismatic Tempered Glass Lens
- LL=Lamp Included ⁹
- POM=Position Oriented Socket

NOTES: 1 150, 175, 200, 250, 320, 350, & 400W only. 2 40°C Ambient environment, except 400W HPS is 25°C ambient. 3 25°C Ambient environment. 4 All lamps are mogul-base. 150W-MH and lower are medium-base. 5 Not available in HPS. 6 Products also available in non-US voltages and 50Hz for international markets. Consult factory for availability and ordering information. 7 Multi-Tap ballast is 120/208/240/277V wired 277V. 8 Triple-Tap ballast is 120/277/347V wired 347V. Add desired voltage to end of catalog number. 9 Must be listed in the order shown and separated by a dash. 10 Lamp is shipped separate from luminaire. Lamp is Cooper designated product based on luminaire requirements. Specified lamps must be ordered as a separate line item.