


# RB4T5

RAB offers energy efficient fluorescent fixtures for large space lighting including warehouses, factories, and distribution centers. The RBAY delivers the high quality needed for these applications with strong, heavy duty 22 gauge rigid housing with no sharp edges. The superior strong-box protective foam case packaging protects the RBAY so it arrives in perfect shape and ready to install.

Color: N/A

Weight: 15.1 lbs



## Lamp Info

Type: T5HO  
 Watts: 216W  
 Shape/Size: N/A  
 Base: N/A  
 ANSI: N/A  
 Hours: 20,000  
 Lamp Lumens: 17,340  
 Efficacy: 72 LPW

## Ballast Info

Type: Prog. Start  
 120V: 2A  
 208V: N/A  
 240V: N/A  
 277V: 0.9A  
 Input Watts: 241W  
 Efficiency: 90%

## Technical Specifications

### UL Listing:

Dry Locations Only. Ceiling Mount Only.

### Housing:

Heavy duty 22 gauge steel housing and wiring box with 1/2" NPS knockouts. Painted white. Easy wiring and maintenance access panel. Includes "Y" hooks.

### Reflector:

Alanod 320G-E with reflectivity of 86%.

### Lamp:

T5HO (not supplied).

### Ballast:

Programmed Start, High Ambient, Universal Voltage  
 120 - 277V (suitable for use with occupancy sensors).

### Ballast Minimum Starting Temperature:

0°F.

### CRI:

85.

### Total Watts:

4x54W.

### Input Volts:

120-277V.

### Input Amps:

.20/.85.

### Ballast Factor:

1.00.

### Base:

Medium Bi Pin.

### Mounts:

Surface or Chain (Y Hooks included).

### Patents:


RAB sensor and fixture designs are protected under U.S. and International Intellectual Property laws.

# RB4T5

RAB offers energy efficient fluorescent fixtures for large space lighting including warehouses, factories, and distribution centers. The RBAY delivers the high quality needed for these applications with strong, heavy duty 22 gauge rigid housing with no sharp edges. The superior strong-box protective foam case packaging protects the RBAY so it arrives in perfect shape and ready to install.

Color: N/A

Weight: 15.1 lbs



## Lamp Info

Type: T5HO  
 Watts: 216W  
 Shape/Size: N/A  
 Base: N/A  
 ANSI: N/A  
 Hours: 20,000  
 Lamp Lumens: 17,340  
 Efficacy: 72 LPW

## Ballast Info

Type: Prog. Start  
 120V: 2A  
 208V: N/A  
 240V: N/A  
 277V: 0.9A  
 Input Watts: 241W  
 Efficiency: 90%

## Technical Specifications

### UL Listing:

Dry Locations Only. Ceiling Mount Only.

### Housing:

Heavy duty 22 gauge steel housing and wiring box with 1/2" NPS knockouts. Painted white. Easy wiring and maintenance access panel. Includes "Y" hooks.

### Reflector:

Alanod 320G-E with reflectivity of 86%.

### Lamp:

T5HO (not supplied).

### Ballast:

Programmed Start, High Ambient, Universal Voltage  
 120 - 277V (suitable for use with occupancy sensors).

### Ballast Minimum Starting Temperature:

0°F.

### CRI:

85.

### Total Watts:

4x54W.

### Input Volts:

120-277V.

### Input Amps:

.20/.85.

### Ballast Factor:

1.00.

### Base:

Medium Bi Pin.

### Mounts:

Surface or Chain (Y Hooks included).

### Patents:

RAB sensor and fixture designs are protected under U.S. and International Intellectual Property laws .