



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



NGH316033E NGS 310+ 3 Pole 1250A Lsi

Eaton Corp

Catalog Number	NGH316033E
Manufacturer	Eaton Corp
Description	Eaton Series G Electronic Molded Case Circuit Breaker, NG-Frame, NG, Digitrip 310 RMS, Electronic LS Trip, Three-Pole, 1600A, 480 Vac, 100 Kaic At 240 Vac, 65 Kaic At 480 Vac, Line and Load, Imperial, 50/60 HZ, 80% Rated
Weight per unit	48.0 (lbs/each)
Product Category	20200113092553

Features

Current Rating	1600 A
dimensions	18.6000 IN X 11.8000 IN X 10.4000 IN
frame	NG
media	Yes
Poles	3
Trip Type	Electronic LS
Voltage Rating	480 VAC

Descriptions

Description	NGS 310+ 3 POLE 1250A LSI
extra long description	ETN NGH316033E NGS 310+ 3 POLE 1250
Features	The Eaton Series G Molded Case Circuit Breaker provides users with unparalleled performance and convenience. A patented contact design features high-speed "blow-open" action, resulting in superior circuit breaker performance. This globally-rated platform offers users high interruption ratings in a compact footprint with ease of in-field configuration applicable to a wide variety of industry and regional requirements. Choose from a selection of thermal magnetic and electronic trip units, available in curren
Long Description	Eaton Series G electronic molded case circuit breaker, NG-frame, NG, Digitrip 310 RMS, Electronic LS trip, Three-pole, 1600A, 480 Vac, 100 kAIC at 240 Vac, 65 kAIC at 480 Vac, Line and load, Imperial, 50/60 Hz, 80% rated
Product Type	NGS 310+ 3 Pole 1250A Lsi

Manufacturer Information

Brand	Eaton
GTIN	00786685950495
Manufacturers Part Number	NGH316033E
UPC	786685950495



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Type Electronic molded case circuit breaker

Packaging

Carton 1

Weight Per each 48

Uses, Certifications, and Standards

Application Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels
and OEMs

Frequency Rating 50 to 60 Hz

standard UL Listed