


RB6T8

RAB offers energy efficient fluorescent fixtures for large space lighting including warehouses, factories, and distribution centers. The RBAY delivers the high quality needed for these applications with strong, heavy duty 22 gauge rigid housing with no sharp edges. The superior strong-box protective foam case packaging protects the RBAY so it arrives in perfect shape and ready to install.

Color: N/A

Weight: 21.0 lbs



Lamp Info

Type: T8
 Watts: 192W
 Shape/Size: N/A
 Base: N/A
 ANSI: N/A
 Hours: 24,000
 Lamp Lumens: 10,784
 Efficacy: 62 LPW

Ballast Info

Type: Instant Start
 120V: 1.45A
 208V: N/A
 240V: N/A
 277V: 0.61A
 Input Watts: 173W
 Efficiency: 111%

Technical Specifications

UL Listing:

Dry Locations Only. Ceiling Mount Only.

Housing:

Heavy duty 22 gauge steel housing and wiring box with 1/2" NPS knockouts. Painted white. Easy wiring and maintenance access panel. Includes "Y" hooks.

Reflector:

AlanoD 320G-E with reflectivity of 86%.

Lamp:

T8 Linear (not supplied).

Ballast:

Instant Start, Universal Voltage 120 - 277V (not suitable for use with occupancy sensors).

Ballast Minimum Starting Temperature:

0°F.

CRI:

85.

Total Watts:

6x32W.

Input Volts:

120-277V.

Input Amps:

1.49/.65.

Ballast Factor:

0.88.

Base:

Medium Bi Pin.

Mounts:

Surface or Chain (Y Hooks included).

Patents:


RAB sensor and fixture designs are protected under U.S. and International Intellectual Property laws.

RB6T8

RAB offers energy efficient fluorescent fixtures for large space lighting including warehouses, factories, and distribution centers. The RBAY delivers the high quality needed for these applications with strong, heavy duty 22 gauge rigid housing with no sharp edges. The superior strong-box protective foam case packaging protects the RBAY so it arrives in perfect shape and ready to install.

Color: N/A

Weight: 21.0 lbs



Lamp Info

Type: T8
 Watts: 192W
 Shape/Size: N/A
 Base: N/A
 ANSI: N/A
 Hours: 24,000
 Lamp Lumens: 10,784
 Efficacy: 62 LPW

Ballast Info

Type: Instant Start
 120V: 1.45A
 208V: N/A
 240V: N/A
 277V: 0.61A
 Input Watts: 173W
 Efficiency: 111%

Technical Specifications

UL Listing:

Dry Locations Only. Ceiling Mount Only.

Housing:

Heavy duty 22 gauge steel housing and wiring box with 1/2" NPS knockouts. Painted white. Easy wiring and maintenance access panel. Includes "Y" hooks.

Reflector:

Alanod 320G-E with reflectivity of 86%.

Lamp:

T8 Linear (not supplied).

Ballast:

Instant Start, Universal Voltage 120 - 277V (not suitable for use with occupancy sensors).

Ballast Minimum Starting Temperature:

0°F.

CRI:

85.

Total Watts:

6x32W.

Input Volts:

120-277V.

Input Amps:

1.49/.65.

Ballast Factor:

0.88.

Base:

Medium Bi Pin.

Mounts:

Surface or Chain (Y Hooks included).

Patents:

RAB sensor and fixture designs are protected under U.S. and International Intellectual Property laws.