



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## NTL873WCC6 Radiant Night Light + SP/3WAY Switch WH

*Pass & Seymour/Legrand*

Catalog Number	NTL873WCC6
Manufacturer	Pass & Seymour/Legrand
Description	15A 120V Single Pole/3-Way Switch With Led Night Light, White
Weight per unit	0.3000 (lbs/each)
Product Category	Gen Purpose Switches

### Features

actuator	Rocker switch
amperage rating	15
Contact Configuration	15A
Contact Rating	120
Mounting Type	Box
Number of Gangs	1.0
Number of Switches	1.0
operating cycles	50000
Poles	Single Pole, 3-Way
Switch Type	Push
Voltage	125.0 V
Voltage Rating	120

### Material, Color, and Finish

Color	White
-------	-------

### Dimensions and Weight

Size	Depth 1.5" x Width 1.6" x Height 2.75"
------	--

### Descriptions

Description	RADIANT NIGHT LIGHT + SP/3WAY SWITCH WH
extra long description	P&S NTL873WCC6 RADIANT NIGHT LIGHT
Features	Nightlight
Long Description	15A 120V Single Pole/3-Way Switch with LED Night Light, White
Product Type	Radiant Night Light + SP/3WAY Switch WH
Special Features	This night light replaces any existing single-pole or 3-way switch devices and offers a hidden sensor that automatically controls the night light, plus five adjustable light levels (including OFF).

### Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007032314
Manufacturers Part Number	NTL-873WCC6
UPC	785007032314



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	FLASHLIGHTS AND BATTERIES
Type	Nightlight

## Trade Size

Amperage	15.0
----------	------

## Packaging

Carton	1
Package	6
Weight Per each	0.3

## Uses, Certifications, and Standards

Application	Residential
environmental conditions	UL94 V2
Mounting	BOX
Operating Temperature	Maximum continuous +115°C, minimum -40°C
standard	CULUS, UL, cULus, UL Listed