



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



RE98 3-1/2X3 Reducing Bushing

Crouse-Hinds

Catalog Number	RE98
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series Re Reducer, Rigid/Imc, End 1: 3-1/2" NPT, End 2: 3" NPT, Feraloy Iron Alloy
Weight per unit	1.3 (lbs/each)
Product Category	Rigid Conduit Fittings - Steel

Features

connection	Threaded
dimensions	4.0000 IN X 1.6200 IN X 4.0000 IN
Material	FERALOY IRON ALLOY

Material, Color, and Finish

Finish	Electrogalvanized With Aluminum Acrylic Painted
--------	---

Dimensions and Weight

Size	3-1/2 To 3 In
------	---------------

Descriptions

Description	3-1/2X3 REDUCING BUSHING
extra long description	CRS-H RE98 3 1/2 TO 3 REDUCING BUSH
Features	Crouse-Hinds series RE, REA and REC explosionproof reducers are used in rigid/IMC conduit systems to reduce conduit hubs to a smaller size (RE), connect two different sizes of conduit together (REC), or enlarge drilled and tapped openings by one NPT size (REA). PLG explosionproof plugs are used for closing threaded conduit hubs.
Long Description	Eaton Crouse-Hinds series RE reducer, Rigid/IMC, End 1: 3-1/2" NPT, End 2: 3" NPT, Feraloy iron alloy
Product Type	3 1/2 to 3 Reducing Bush
Special Features	Reducing fitting

Manufacturer Information

Brand	Eaton
GTIN	00782274592107
Manufacturers Part Number	RE98
UPC	782274592107

Taxonomies, Classifications, and Categories

Category Description	Locknuts, Bushings, Re-Bushings, Re-Washers, Threaded Plugs, Knockout Plugs
Type	REDUCER



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	2
Weight Per each	1.25

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Industrial Facilities/Factories - Other
Enclosure	Class I Div 1 2 Group A B C D, Class II Div 1 Group E F G, Class II
	Div 2 Group F G, Class III
standard	UL 886, CSA C22.2