

P8022 Series

7.25 inch LED New Construction and Remodel • Wet Location



Specifications:

Description:

The P8022 delivers a solution for flush mount and recessed applications, for both residential and commercial markets. In addition, the P8022 is wet located, Title 24 - JA8 - 2016 and is a cost effective solution for fire rated application. The P8022 luminaire unites performance, cost and safety benefits.

Construction:

- Diffused polycarbonate lens controls direct glare from the LEDs
- Simple snap in installation for J-Box and Twist and Push for recessed housings
- Die-cast aluminum construction with a powder coat paint finish
- Can be installed in a 4" J-Box and 6", 5" and 4" recessed housing. (All hardware included)
- Lumen output and distribution comparable to a 100W incandescent lamp
- Suitable for use in IC or NON-IC Applications with 25°C (77°F) continuous room side ambient temperature.
- Provided with quick link for use with E26 Edison Base adapter
- This product is not available for sale into the State of California.

Performance:


Input Power	17W
Input Voltage	120V
Input Frequency	60Hz
Lumens/LPW	1050/67 (LM-79)
CCT	3000K
CRI	90+
Life	50,000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Min. Start Temp	-30° C
Max. Operating Temp	30° C
Warranty	5 yrs.
Labels	cCSAus classified for wet locations ENERGY STAR® qualified California Title 24 - JA8-2016

P8022-28-30K

Images:




Dimensions:


Diameter: 7.25"
Height: 1.1875"


Included Mounting Options:

Recessed Mount with Quick-Link




Recessed Adapter




E26 Edison Base Adapter



J-Box Mount with Quick-Link



J-Box Adapter



Catalog number:

Base	Finish	Color Temp	CRI
P8022	20 - Bronze 28 - White 31 - Black 82 - Metallic Gray	30K - 3000K	BLANK - 90 CRI

Photometrics:

P8022-28-30K

ELECTRICAL DATA	P8022-28-30K
------------------------	---------------------

Input Voltage	120V
Input Frequency	60 Hz
Constant Current Output	146mA
Power Factor	≥0.90
THD	<20%
EMI Filtering	FCC 47CFR Part 15, Class B
Operating Temperature	-30°C to 30°C
Dimming	Yes*

Over-voltage, over-current, short-circuit protected

*See Dimming Notes for more information

Dimming Notes:

P8022-28-30K

P8022 is designed to be compatible with many Triac/Forward Phase controls. LED rated dimmer controls may offer favorable dimming performance.

The following is a partial list of known compatible dimmer controls:

Triac/Forward Phase Controls

Lutron	AYCL-153P
Lutron	AY-600
Lutron	TGCL-153P
Leviton	6674
Leviton	6672

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.

P8022 Series

7.25 inch LED New Construction and Remodel • Wet Location



Specifications:

Description:

The P8022 delivers a solution for flush mount and recessed applications, for both residential and commercial markets. In addition, the P8022 is wet located, Title 24 - JA8 - 2016 and is a cost effective solution for fire rated application. The P8022 luminaire unites performance, cost and safety benefits.

Construction:

- Diffused polycarbonate lens controls direct glare from the LEDs
- Simple snap in installation for J-Box and Twist and Push for recessed housings
- Die-cast aluminum construction with a powder coat paint finish
- Can be installed in a 4" J-Box and 6", 5" and 4" recessed housing. (All hardware included)
- Lumen output and distribution comparable to a 100W incandescent lamp
- Suitable for use in IC or NON-IC Applications with 25°C (77°F) continuous room side ambient temperature.
- Provided with quick link for use with E26 Edison Base adapter
- This product is not available for sale into the State of California.

Performance:

Input Power	17W
Input Voltage	120V
Input Frequency	60Hz
Lumens/LPW	1050/67 (LM-79)
CCT	3000K
CRI	90+
Life	50,000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Min. Start Temp	-30° C
Max. Operating Temp	30° C
Warranty	5 yrs.
Labels	cCSAus classified for wet locations ENERGY STAR® qualified California Title 24 - JA8-2016


P8022-28-30K

Images:




Dimensions:

Diameter: 7.25"
Height: 1.1875"




Included Mounting Options:

Recessed Mount with Quick-Link




Recessed Adapter




E26 Edison Base Adapter



J-Box Mount with Quick-Link



J-Box Adapter



Catalog number:

Base	Finish	Color Temp	CRI
P8022	20 - Bronze 28 - White 31 - Black 82 - Metallic Gray	30K - 3000K	BLANK - 90 CRI

Photometrics:

P8022-28-30K

ELECTRICAL DATA	P8022-28-30K
------------------------	---------------------

Input Voltage	120V
Input Frequency	60 Hz
Constant Current Output	146mA
Power Factor	≥0.90
THD	<20%
EMI Filtering	FCC 47CFR Part 15, Class B
Operating Temperature	-30°C to 30°C
Dimming	Yes*

Over-voltage, over-current, short-circuit protected

*See Dimming Notes for more information

Dimming Notes:

P8022-28-30K

P8022 is designed to be compatible with many Triac/Forward Phase controls. LED rated dimmer controls may offer favorable dimming performance.

The following is a partial list of known compatible dimmer controls:

Triac/Forward Phase Controls

Lutron	AYCL-153P
Lutron	AY-600
Lutron	TGCL-153P
Leviton	6674
Leviton	6672

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.