

# Specifications

## Eaton REN-50

Eaton Bussmann series REN fuse, time lag, non current-limiting, Industrial and commercial structures, 50 A, Class H, Non-indicating, Ferrule end x ferrule end, 10 kAIC, Standard, 10, 250 V



Photo is representative



### General specifications

<b>PRODUCT NAME</b>	Eaton Bussmann series REN fuse
<b>CATALOG NUMBER</b>	REN-50
<b>UPC</b>	051712100502
<b>EAN</b>	5027590465793
<b>PRODUCT LENGTH/DEPTH</b>	0.82 in
<b>PRODUCT HEIGHT</b>	2.98 in
<b>PRODUCT WIDTH</b>	0.82 in
<b>PRODUCT WEIGHT</b>	0.12 lb
<b>WARRANTY</b>	Not Applicable
<b>COMPLIANCES</b>	Not Applicable

## Electrical rating

AMPERAGE RATING	50 A
INTERRUPT RATING	10 kAIC
VOLTAGE RATING	250 V

## General information

CLASS	Class H
CONNECTION	Ferrule end x ferrule end
FUSE INDICATOR	Non-indicating
QUANTITY	10
SPECIAL FEATURES	Super lag, time lag, non current-limiting

## Physical details

PACKAGING TYPE	Standard
----------------	----------

## Resources

CATALOGS	<a href="#">Bussmann series complete full line catalog no. 1007</a> <a href="#">REN-50~SUPER LAG RENEWABLE FUSE 50/250</a>
MULTIMEDIA	<a href="#">Bussmann series Fuseology</a>
SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - REN-50</a>

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

