

Specifications



Photo is representative



Eaton S20N11P76P

Eaton General-Purpose Encapsulated Transformer, EP, Single-phase, PV: 240 X 480V, Taps: None, SV: 120/240V, 115°C, .75 kVA, Alum windings, Frame: 58AP, Indoor-Outdoor

General specifications

PRODUCT NAME	Eaton General purpose encapsulated transformer
CATALOG NUMBER	S20N11P76P
UPC	786680233852
PRODUCT LENGTH/DEPTH	5.99 in
PRODUCT HEIGHT	11.68 in
PRODUCT WIDTH	4.99 in
PRODUCT WEIGHT	22 lb
COMPLIANCES	Not Applicable
CERTIFICATIONS	UL Listed



Powering Business Worldwide

Physical Attributes	
COIL MATERIAL	Aluminum
DESIGN	EP
ENCLOSURE	NEMA 3R
FRAME	58AP
TAP SIZE	None
TYPE	General-Purpose Encapsulated Transformer
WIRING CONNECTION	3A

Miscellaneous	
WEATHERSHIELD	Indoor-Outdoor

Performance Ratings	
FREQUENCY RATING	60 Hz
PHASE	Single-phase
PRIMARY VOLTAGE	240 V, 480 V
SECONDARY VOLTAGE	120/240 V
TEMPERATURE RISE	115 °C rise
VOLT AMPERE RATING	0.75 kVA

Resources	
CATALOGS	Commercial Distribution Transformers, Volume 2, Tab 2
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - S20N11P76P

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc
 Eaton House
 30 Pembroke Road
 Dublin 4, Ireland
 Eaton.com

Follow us on social media to get the latest product and support information.

