ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

PLT1MC Cable Tie, 3.9L (99MM), Miniature, Nylon, Natural

Panduit Corporation

Catalog Number	PLT1MC
Manufacturer	Panduit Corporation
Description	The PLT1M-C Cable Tie Provides Dependable Bundling For Small Indoor Installations and General-Purpose Routing. Miniature Cross Section, 3.9 In (99MM) Long With 18 LB (80 N) Minimum Loop Tensile Strength and A 0.06–0.87 In (1.5–22.1MM) Bundle Diameter Range. It Is Natural Nylon 6.6 For Consistent Routing and Organization. Operating Range -76 to 185°F (-60 to 85°C). Use With GTS-E, GS2B-E, PTS, PPTS, and STS2 Tools. STD. PKG. Qty. 100.
Weight per unit	0.1500 (lbs/each)
Product Category	Cable Ties & Wraps

Features

media	Yes
Tensile Strength	18

Dimensions and Weight

Length	3.94
Thickness	0.05

Descriptions

Description	CABLE TIE, 3.9L (99MM), MINIATURE, NYLON, NATURAL
extra long description	PAN PLT1M-C Cable Tie, Natural, PA6
Long Description	The PLT1M-C cable tie provides dependable bundling for small indoor installations and general-purpose routing. Miniature cross section, 3.9 in (99mm) long with 18 lb (80 N) minimum loop tensile strength and a 0.06–0.87 in (1.5–22.1mm) bundle diameter range. It is natural Nylon 6.6 for consistent routing and organization. Operating range -76 to 185°F (-60 to 85°C). Use with GTS-E, GS2B-E, PTS, PPTS, and STS2 tools. Std. pkg. qty. 100.
Product Type	Cable Tie, Natural, PA6.6, 3.9"L (99 MM), 18LB, PK100
Special Features	Indoor

Manufacturer Information

Brand	Panduit®
GTIN	00074983540044
Manufacturers Part Number	PLT1M-C
UPC	074983540044

Taxonomies, Classifications, and Categories

Category Description	Screws, Bolts, Staples, Jack Chains, Washers & TY-Raps
Type	Premium Cable Tie

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	100
Package	1000
Weight Per each	0.15

Uses, Certifications, and Standards

standard	CSA Certified, UL Recognized (File #E56854), UL 62275 Compliant (Type 2, 21), RoHS Compliant