



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



S420CLCN00 2" X CL SS304 Nipple

Calbrite

| | |
|------------------|---|
| Catalog Number | S420CLCN00 |
| Manufacturer | Calbrite |
| Description | 2" X Close Rigid Stainless Steel 304 Conduit Nipple |
| Weight per unit | 0.3800 (lbs/each) |
| Product Category | Steel |

Features

| | |
|------------------|------------------------|
| Inside Diameter | 2.07 |
| Material | Stainless Steel - 304L |
| outside diameter | 2.375 |
| Wall Thickness | 0.153 |

Material, Color, and Finish

| | |
|--------|--------------------|
| Color | Polished Silver |
| Finish | #4 Polished Finish |

Dimensions and Weight

| | |
|--------|---|
| Length | 2 |
|--------|---|

Descriptions

| | |
|------------------------|--|
| Description | 2" X CL SS304 NIPPLE |
| extra long description | CAL S420CLCN00 2 X CL SS304 NIP |
| Features | Stainless steel rigid conduit nipples are available in 304 or 316 and are used to extend conduit systems and can be connected to boxes, enclosures, fittings, and other lengths of conduit |
| Long Description | 2" X Close Rigid Stainless Steel 304 Conduit Nipple |
| Product Type | 2 X CL SS304 Nip |
| Short Description | SS_RGD NPL_304 |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | CALBRITE |
| GTIN | 00847656003890 |
| Manufacturers Part Number | S420CLCN00 |
| UPC | 847656003890 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---------------|
| Category Description | RIGID NIPPLES |
| Type | Nipple |

Trade Size

| | |
|------------|---|
| Trade Size | 2 |
|------------|---|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

| | |
|----------------------|------|
| Carton..... | 1 |
| Weight..... | 0.38 |
| Weight Per each..... | 0.38 |

Uses, Certifications, and Standards

| | |
|-------------------------|------|
| Temperature Rating..... | 1600 |
|-------------------------|------|