



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PSG60F24RM PSG PWR Supply

Eaton Corp

Catalog Number	PSG60F24RM
Manufacturer	Eaton Corp
Description	Eaton PSG Series Power Supply, Aluminum, 320-575 Vac, 47-63 HZ, Finger-Safe Terminals, 24 VDC Output, Three-Phase, 960W Output Power, -25°C-75°C Operating Temp
Weight per unit	2.0 (lbs/each)
Product Category	DC Power Supplies

Features

dimensions	7.0000 IN X 6.5000 IN X 3.0000 IN
media	Yes
Phase	Three-phase

Descriptions

Description	PSG PWR SUPPLY
extra long description	ETN PSG60F24RM PSG Power Supply
Features	The PSG line of general purpose power supplies is used in a wide variety of industrial control applications. Applications include communication networks, sensors, PLCs and many other electrical systems. Each model is equipped with the options of a rugged metal or plastic housing, heavy-duty screw or finger-safe terminals and a variety of protection features. The PSG line offers the flexibility of operating with a universal input voltage of 100–240 Vac. It also provides system protection and continuous oper
Long Description	Eaton PSG series Power Supply, Aluminum, 320-575 Vac, 47-63 Hz, Finger-safe terminals, 24 Vdc output, Three-phase, 960W output power, -25°C-75°C operating temp
Product Type	PSG Power Supply

Manufacturer Information

Brand	Eaton
GTIN	00786685683577
Manufacturers Part Number	PSG60F24RM
UPC	786685683577

Taxonomies, Classifications, and Categories

Category Description	POWER SUPPLIES
Type	General purpose power supply

Packaging

Carton	1
Weight Per each	2



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Facility: Power Distribution and Control
Frequency Rating	47-63 Hz
standard	IEC Rated,EN Listed,CSA Std. C22.2,UL 508,CE Marked,RoHS
	Compliant