

Eaton PVML-7-UNV34

Catalog Number: PVML-7-UNV34

Eaton Crouse-Hinds series Champ Pro PVML LED fixture, Cool white, 175W HID equivalent, No guard, Glass lens, 7000 lumens, 127 lm/W, Die cast aluminum, No mounting module, Type V, 347-480 Vac, 61W

General specifications



Photo is representative

Product Name	Catalog Number
Eaton Crouse-Hinds series Champ Pro PVML LED light fixture	PVML-7-UNV34
	UPC
	662276906143
Product Length/Depth	Product Height
13 in	13.13 in
Product Width	Product Weight
12.75 in	20.8 lb

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

IEC

NEMA Rating

4X

Ingress protection (IP) ratings

IP66

Product specifications

Lumens

7000

Lumens per watt

127

Color temperature

Cool white

Mounting Method

No mounting module

Optical distribution

Type V

Guard type

No guard

Voltage rating

347-480 Vac

Frequency rating

50/60 Hz

Wattage

61W

Dimming

Dimmable driver

Power factor

> 0.90

Equivalent luminaire

175W HID

Material

Die cast aluminum

Lens material

Heat and impact resistant glass

Resources

3D models

[SP3D Design Package - Champ Pro PVML Industrial LED Light](#)

[Fixtures](#)

[Brochures](#)

Crouse-Hinds series Champ Pro PVML LED Luminaires - 3,000 to 13,000 lumens brochure

Crouse-Hinds series DLC approved lighting products

Crouse-Hinds series Global LED lighting portfolio

Crouse-Hinds series industrial LED lighting solutions

Catalogs

Crouse-Hinds series Champ Pro PVML LED luminaires - 3,000 to 13,000 lumens catalog page

Certification reports

Champ Pro PVML Industrial LED Light Fixtures Canadian certification

Champ Pro PVML Industrial LED Light Fixtures UL certification

EC Declaration of Conformity - Crouse-Hinds series Champ Pro PVML LED Luminaires

Installation instructions

IF 1888 - Champ VMVL and PVML Driver Replacement

IF 1882 - Champ VMVL and PVML LED luminaires

Specifications and datasheets

Eaton Specification Sheet - PVML-7-UNV34

Champ Pro PVM Industrial LED



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton PVML-7-UNV34

Catalog Number: PVML-7-UNV34

Eaton Crouse-Hinds series Champ Pro PVML LED fixture, Cool white, 175W HID equivalent, No guard, Glass lens, 7000 lumens, 127 lm/W, Die cast aluminum, No mounting module, Type V, 347-480 Vac, 61W

General specifications



Photo is representative

Product Name	Catalog Number
Eaton Crouse-Hinds series Champ Pro PVML LED light fixture	PVML-7-UNV34
	UPC
	662276906143
Product Length/Depth	Product Height
13 in	13.13 in
Product Width	Product Weight
12.75 in	20.8 lb

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

IEC

NEMA Rating

4X

Ingress protection (IP) ratings

IP66

Product specifications

Lumens

7000

Lumens per watt

127

Color temperature

Cool white

Mounting Method

No mounting module

Optical distribution

Type V

Guard type

No guard

Voltage rating

347-480 Vac

Frequency rating

50/60 Hz

Wattage

61W

Dimming

Dimmable driver

Power factor

> 0.90

Equivalent luminaire

175W HID

Material

Die cast aluminum

Lens material

Heat and impact resistant glass

Resources

3D models

SP3D Design Package - Champ Pro PVML Industrial LED Light

Fixtures

Brochures

Crouse-Hinds series Champ Pro PVML LED Luminaires - 3,000 to 13,000 lumens brochure

Crouse-Hinds series DLC approved lighting products

Crouse-Hinds series Global LED lighting portfolio

Crouse-Hinds series industrial LED lighting solutions

Catalogs

Crouse-Hinds series Champ Pro PVML LED luminaires - 3,000 to 13,000 lumens catalog page

Certification reports

Champ Pro PVML Industrial LED Light Fixtures Canadian certification

Champ Pro PVML Industrial LED Light Fixtures UL certification

EC Declaration of Conformity - Crouse-Hinds series Champ Pro PVML LED Luminaires

Installation instructions

IF 1888 - Champ VMVL and PVML Driver Replacement

IF 1882 - Champ VMVL and PVML LED luminaires

Specifications and datasheets

Eaton Specification Sheet - PVML-7-UNV34

Champ Pro PVM Industrial LED



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)