



# NEW PRODUCT INFORMATION

## KolourOne Panel Array 2.0 7W MR16 LED lamp





### Applications

- Indoor residential and commercial lighting
- Entertainment lighting
- Down lighting
- Display lighting
- Accent lighting

### Features

- Direct replacement for Halogen MR16 lamps (20-35W) uses only 7 Watts
- Exacting color consistency
- High lumen output
- Tight beam focus and intensity
- Multiple CCT and beam angle options
- Uniform luminance pattern
- Longer throw distances
- Light weight
- Environmentally friendly; no UV or IR radiation
- High efficiency: long "true" life; 25,000 hours\*
- Available in white finish
- This product is registered with the US DOE Lighting Facts program
- 3 year warranty\*\*
- ENERGY STAR® qualified



Not for use with dimmers.  
Recommended for use with magnetic transformers.  
Compatibility with electronic transformers minimum load requirement must be verified.

\* All items are designed for 30,000 hours. 25,000 hours represents current stage of ENERGY STAR® qualification.

\*\* See separate warranty for complete terms and conditions.

### KolourOne Panel Array 2.0 MR16 LED Lamps



Item Number	Lamp Description	Watts	Volts	CCT	CRI	Lumens	Beam	Life/Hours
<b>MR16 - PANEL ARRAY 2.0</b>								
S8845 <sup>†</sup>	7MR16/LED/40°/27K/WH/PA 2.0	7	12	2700	87	430	40	25,000
S8846 <sup>†</sup>	7MR16/LED/40°/35K/WH/PA 2.0	7	12	3500	85	435	40	25,000
S8847	7MR16/LED/40°/50K/WH/PA 2.0	7	12	5000	85	440	40	25,000

<sup>†</sup> ENERGY STAR® qualified.



National Toll-Free: 800.43.SATCO (800.437.2826) www.satco.com

Distribution Centers: New York, Florida, Texas, Washington, California, Puerto Rico

Corporate Offices: 110 Heartland Blvd., Brentwood, NY 11717 800.437.2826 631.243.2022 Fax 631.243.2027



# NEW PRODUCT INFORMATION

## KolourOne Panel Array 2.0 7W MR16 LED lamp





### Applications

- Indoor residential and commercial lighting
- Entertainment lighting
- Down lighting
- Display lighting
- Accent lighting

### Features

- Direct replacement for Halogen MR16 lamps (20-35W) uses only 7 Watts
- Exacting color consistency
- High lumen output
- Tight beam focus and intensity
- Multiple CCT and beam angle options
- Uniform luminance pattern
- Longer throw distances
- Light weight
- Environmentally friendly; no UV or IR radiation
- High efficiency: long "true" life; 25,000 hours\*
- Available in white finish
- This product is registered with the US DOE Lighting Facts program
- 3 year warranty\*\*
- ENERGY STAR® qualified



Not for use with dimmers.  
Recommended for use with magnetic transformers.  
Compatibility with electronic transformers minimum load requirement must be verified.

\* All items are designed for 30,000 hours. 25,000 hours represents current stage of ENERGY STAR® qualification.

\*\* See separate warranty for complete terms and conditions.

### KolourOne Panel Array 2.0 MR16 LED Lamps



Item Number	Lamp Description	Watts	Volts	CCT	CRI	Lumens	Beam	Life/ Hours
<b>MR16 - PANEL ARRAY 2.0</b>								
S8845 <sup>†</sup>	7MR16/LED/40'/27K/WH/PA 2.0	7	12	2700	87	430	40	25,000
S8846 <sup>†</sup>	7MR16/LED/40'/35K/WH/PA 2.0	7	12	3500	85	435	40	25,000
S8847	7MR16/LED/40'/50K/WH/PA 2.0	7	12	5000	85	440	40	25,000

<sup>†</sup> ENERGY STAR® qualified.



National Toll-Free: 800.43.SATCO (800.437.2826) www.satco.com

Distribution Centers: New York, Florida, Texas, Washington, California, Puerto Rico

Corporate Offices: 110 Heartland Blvd., Brentwood, NY 11717 800.437.2826 631.243.2022 Fax 631.243.2027