





GE
Lighting

77906 - Q35MR16HIR/CCG35

GE halogen 35 watt MR16 1-pack

- Compact size, white light, excellent color Precise optical control delivers a concentrated beam of light right where it's needed
- Estimated yearly energy costs \$4.22 based on 3 hours per day \$0.11 per kWh
- GE halogen bulbs deliver crisp, white light. This unsurpassed light quality is ideal for adding depth, drama and interest inside and outside your home. Use GE halogen MR16 bulbs in indoor track and recessed lighting and outdoor directional lighting to create a dramatic effect
- Input Voltage = 12 volts
- Lasts 4.6 years based on 3 hours per day usage
- MR16 shape with 2-Pin (GU5.3) base for use directional fixtures such as recessed can lighting

RoHs Compliant



GENERAL CHARACTERISTICS

Lamp Type	Halogen - MR
Bulb	MR16
Base	2-Pin (GU5.3)
Filament	CC-8
Bulb Finish	Clear
Rated Life	5000.0 hrs
Lamp Enclosure Type (LET)	Covered glass
Primary Application	Indoor Floodlight

PHOTOMETRIC CHARACTERISTICS

Center Beam Candlepower (CBCP)	2000.0
Color Temperature	2950.0 K
Beam Spread (10% hor)	75° Cone
Abstract Values	
Beam Spread	35.0 °

ELECTRICAL CHARACTERISTICS

Wattage	35.0
Voltage	12.0

DIMENSIONS

Maximum Overall Length (MOL)	1.7700 in(45.0 mm)
Bulb Diameter (DIA)	2.000 in(50.8 mm)

PRODUCT INFORMATION

Product Code	77906
Description	Q35MR16HIR/CCG35
Standard Package	BUNDLE
Standard Package GTIN	10043168779064
Standard Package Quantity	20
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	20
UPC	043168779067





GE
Lighting

77906 - Q35MR16HIR/CCG35

GE halogen 35 watt MR16 1-pack

- Compact size, white light, excellent color Precise optical control delivers a concentrated beam of light right where it's needed
- Estimated yearly energy costs \$4.22 based on 3 hours per day \$0.11 per kWh
- GE halogen bulbs deliver crisp, white light. This unsurpassed light quality is ideal for adding depth, drama and interest inside and outside your home. Use GE halogen MR16 bulbs in indoor track and recessed lighting and outdoor directional lighting to create a dramatic effect
- Input Voltage = 12 volts
- Lasts 4.6 years based on 3 hours per day usage
- MR16 shape with 2-Pin (GU5.3) base for use directional fixtures such as recessed can lighting

RoHs Compliant



GENERAL CHARACTERISTICS

Lamp Type	Halogen - MR
Bulb	MR16
Base	2-Pin (GU5.3)
Filament	CC-8
Bulb Finish	Clear
Rated Life	5000.0 hrs
Lamp Enclosure Type (LET)	Covered glass
Primary Application	Indoor Floodlight

PHOTOMETRIC CHARACTERISTICS

Center Beam Candlepower (CBCP)	2000.0
Color Temperature	2950.0 K
Beam Spread (10% hor)	75° Cone
Abstract Values	
Beam Spread	35.0 °

ELECTRICAL CHARACTERISTICS

Wattage	35.0
Voltage	12.0

DIMENSIONS

Maximum Overall Length (MOL)	1.7700 in(45.0 mm)
Bulb Diameter (DIA)	2.000 in(50.8 mm)

PRODUCT INFORMATION

Product Code	77906
Description	Q35MR16HIR/CCG35
Standard Package	BUNDLE
Standard Package GTIN	10043168779064
Standard Package Quantity	20
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	20
UPC	043168779067