

Eaton REN-20

Catalog Number: REN-20

Eaton Bussmann series REN fuse, time lag, non current-limiting, Industrial and commercial structures, 20 A, Class H, Non-indicating, Ferrule end x ferrule end, 10 kAIC, Standard, 10, 250 V

General specifications



Photo is representative

| | |
|--------------------------------|-----------------------|
| Product Name | Catalog Number |
| Eaton Bussmann series REN fuse | REN-20 |
| UPC | EAN |
| 051712100205 | 5027590098250 |
| Product Length/Depth | Product Height |
| 0.56 in | 2 in |
| Product Width | Product Weight |
| 0.56 in | 0.41 lb |
| Warranty | Compliances |
| Not Applicable | Not Applicable |
| | RoHS Compliant |

Electrical rating

Amperage Rating

20 A

Interrupt rating

10 kAIC

Voltage rating

250 V

Physical details

Packaging type

Standard

General information

Class

Class H

Connection

Ferrule end x ferrule end

Fuse indicator

Non-indicating

Quantity

10

Special features

Super lag, time lag, non current-limiting

Resources

Catalogs

[REN-20~SUPER LAG RENEWABLE FUSE 20/250](#)

[Bussmann series complete full line catalog no. 1007](#)

Multimedia

[Bussmann series Fuseology](#)

Specifications and datasheets

[Eaton Specification Sheet - REN-20](#)