

Eaton REN-30

Catalog Number: REN-30

Eaton Bussmann series REN fuse, time lag, non current-limiting, Industrial and commercial structures, 30 A, Class H, Non-indicating, Ferrule end x ferrule end, 10 kAIC, Standard, 10, 250 V

General specifications



| | |
|--------------------------------|-----------------------------|
| Product Name | Catalog Number |
| Eaton Bussmann series REN fuse | REN-30 |
| UPC | Product Length/Depth |
| 051712100304 | 2 in |
| Product Height | Product Width |
| 0.56 in | 0.56 in |
| Product Weight | Warranty |
| 0.55 lb | Not Applicable |
| Compliances | |
| Not Applicable | |

Electrical rating

Amperage Rating

30 A

Interrupt rating

10 kAIC

Voltage rating

250 V

Physical details

Packaging type

Standard

General information

Class

Class H

Connection

Ferrule end x ferrule end

Fuse indicator

Non-indicating

Quantity

10

Special features

Super lag, time lag, non current-limiting

Resources

Catalogs

[Bussmann series complete full line catalog no. 1007](#)

[Bussmann series full line catalog 1007, section 01- low voltage branch circuit fuses](#)

[REN-30~SUPER LAG RENEWABLE FUSE 30/250](#)

Multimedia

[Bussmann series Fuseology](#)

Specifications and datasheets

[Eaton Specification Sheet - REN-30](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)