

Specifications

Eaton REN-50

Eaton Bussmann series REN fuse, time lag, non current-limiting, Industrial and commercial structures, 50 A, Class H, Non-indicating, Ferrule end x ferrule end, 10 kAIC, Standard, 10, 250 V



Photo is representative



General specifications

| | |
|-----------------------------|--------------------------------|
| PRODUCT NAME | Eaton Bussmann series REN fuse |
| CATALOG NUMBER | REN-50 |
| UPC | 051712100502 |
| EAN | 5027590465793 |
| PRODUCT LENGTH/DEPTH | 0.82 in |
| PRODUCT HEIGHT | 2.98 in |
| PRODUCT WIDTH | 0.82 in |
| PRODUCT WEIGHT | 0.12 lb |
| WARRANTY | Not Applicable |
| COMPLIANCES | Not Applicable |

Electrical rating

| | |
|------------------|---------|
| AMPERAGE RATING | 50 A |
| INTERRUPT RATING | 10 kAIC |
| VOLTAGE RATING | 250 V |

General information

| | |
|------------------|---|
| CLASS | Class H |
| CONNECTION | Ferrule end x ferrule end |
| FUSE INDICATOR | Non-indicating |
| QUANTITY | 10 |
| SPECIAL FEATURES | Super lag, time lag, non current-limiting |

Physical details

| | |
|----------------|----------|
| PACKAGING TYPE | Standard |
|----------------|----------|

Resources

| | |
|-------------------------------|---|
| CATALOGS | Bussmann series complete full line catalog no. 1007 REN-50~SUPER LAG RENEWABLE FUSE 50/250 |
| MULTIMEDIA | Bussmann series Fuseology |
| SPECIFICATIONS AND DATASHEETS | Eaton Specification Sheet - REN-50 |

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



Specifications

Eaton REN-50

Eaton Bussmann series REN fuse, time lag, non current-limiting, Industrial and commercial structures, 50 A, Class H, Non-indicating, Ferrule end x ferrule end, 10 kAIC, Standard, 10, 250 V



Photo is representative



General specifications

| | |
|-----------------------------|--------------------------------|
| PRODUCT NAME | Eaton Bussmann series REN fuse |
| CATALOG NUMBER | REN-50 |
| UPC | 051712100502 |
| EAN | 5027590465793 |
| PRODUCT LENGTH/DEPTH | 0.82 in |
| PRODUCT HEIGHT | 2.98 in |
| PRODUCT WIDTH | 0.82 in |
| PRODUCT WEIGHT | 0.12 lb |
| WARRANTY | Not Applicable |
| COMPLIANCES | Not Applicable |



Powering Business Worldwide

Electrical rating

| | |
|------------------|---------|
| AMPERAGE RATING | 50 A |
| INTERRUPT RATING | 10 kAIC |
| VOLTAGE RATING | 250 V |

General information

| | |
|------------------|---|
| CLASS | Class H |
| CONNECTION | Ferrule end x ferrule end |
| FUSE INDICATOR | Non-indicating |
| QUANTITY | 10 |
| SPECIAL FEATURES | Super lag, time lag, non current-limiting |

Physical details

| | |
|----------------|----------|
| PACKAGING TYPE | Standard |
|----------------|----------|

Resources

| | |
|-------------------------------|---|
| CATALOGS | Bussmann series complete full line catalog no. 1007 REN-50~SUPER LAG RENEWABLE FUSE 50/250 |
| MULTIMEDIA | Bussmann series Fuseology |
| SPECIFICATIONS AND DATASHEETS | Eaton Specification Sheet - REN-50 |

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

