



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



T2535153S 7.5 Kva 1PH 240/480 Transformer *Acme Electric*

Catalog Number	T2535153S
Manufacturer	Acme Electric
Description	Low Voltage Distribution Transformer - Single Phase, 240X480 - 120/240V, 7.5kva
Weight per unit	115.0 (lbs/each)
Product Category	Single Phase Non Ventilated to

Features

Fuse Rating	Primary: 40 AMP For 240 V, 20 AMP For 480 V, Secondary: 80 AMP For 120 V
pallet quantity	6
Primary Voltage	240 X 480
product category	Dry Type Distribution Transformer
Secondary Voltage	120/240

Dimensions and Weight

Height	15.19
Length	10.84
Width	13.5

Descriptions

Construction	ENCAPSULATED
Description	7.5 KVA 1PH 240/480 TRANSFORMER
extra long description	ACME T2535153S TFMR 1PH 7.5KVA 240X
Long Description	Low Voltage Distribution Transformer - Single Phase, 240X480 - 120/240V, 7.5kVA
Product Type	Dry Type Distribution Transformer
Special Features	Encapsulated core and coil; Shielded for cleaner power; Encapsulated and completely enclosed design electrical grade silica and resin compounds completely enclose the core and coil to seal out all moisture and air, UL type 3R enclosure for indoor or outdoor service, encapsulation eliminates corrosion and insulation deterioration; Quiet operation with sound levels well below NEMA standards; 10-year limited warranty

Manufacturer Information

Brand	ACME ELECTRIC
GTIN	00047503734056
Manufacturers Part Number	T2535153S
UPC	047503734056



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	1 PHASE TRANSFORMERS
Type	Distribution Transformer

Packaging

Carton	1
Weight Per each	115

Uses, Certifications, and Standards

Enclosure	NEMA 3R Steel
Mounting standard	WALL UL 506, UL File Number E79947V1, UL Control Number 50B8, UL Insulation Number H3221, CSA Certified, OSHA Compliant, ANSI, IEEE
Temperature Rating	115 DEG C Rise