

Project Name

Location

Prepared By



SATCO S29391

22W/LED/HID/5000K/100-277V E26

Notes

[www] 02-12-2023, 19:07:34

General

Status	Discontinued
Substitute	S49391
Watts	22W
Incandescent Equivalent	150W
Fluorescent Equivalent	40W
HID Equivalent	100W
Volts	120V-277V
Shape	Corncob
Base	Medium
ANSI Base	E26
Finish	Clear
CCT (Kelvin)	5000K
Temperature	Natural Light
CRI	80+
Lumens	2950L
Beam Spread	300
Dimmable	Non-Dimmable
Hours Rated	50000
Product Category	Corncob
Technology	LED
Min Compartment Size	Length: 8.5 in. Width: 6 in. Depth: 6 in.
Ballasting Requirements	Ballast Bypass- Direct wire only 100V-277V

Electrical

Working Voltage	AC 90-305V
Operating Frequency	50/60Hz
Power Factor	>.9
Operating Position	Universal
Operating Temperature	-20C (-4F) to +40C (+104F)

Physical

MOL	7.56
MOD	2.75
Lens Finish	Clear
Weight (lb.)	0.96

Additional Information

Additional Info	Replaces HID, CFL, and Incandescent; UL approved for totally enclosed fixtures; For outdoor & indoor use; Emits no UV light / Contains no Mercury (Hg)
Rated For Enclosed Fixture	Yes
IP Rating	IP65
Installation Notes	Not for use in vapor tight fixtures.
Warranty	5 Year Limited - Hi-Pro

Compliance

Safety Listing	cULus - Certified; cULus - Classified; cULus - Listed
Location Rating	Damp
DLC Approved	No
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
Colorado Status	Lawful for sale
Hawaii Status	Lawful for sale
Nevada Status	Lawful for sale
Vermont Status	Lawful for sale
Washington Status	Lawful for sale
RoHS Compliant	Yes
FCC Compliant	Yes
SDS Sheet	LED_Lamp

Project Name

Location

Prepared By



SATCO S29391

22W/LED/HID/5000K/100-277V E26

Notes

[www] 02-12-2023, 19:07:34

General	
Status	Discontinued
Substitute	S49391
Watts	22W
Incandescent Equivalent	150W
Fluorescent Equivalent	40W
HID Equivalent	100W
Volts	120V-277V
Shape	Corncob
Base	Medium
ANSI Base	E26
Finish	Clear
CCT (Kelvin)	5000K
Temperature	Natural Light
CRI	80+
Lumens	2950L
Beam Spread	300
Dimmable	Non-Dimmable
Hours Rated	50000
Product Category	Corncob
Technology	LED
Min Compartment Size	Length: 8.5 in. Width: 6 in. Depth: 6 in.
Ballasting Requirements	Ballast Bypass- Direct wire only 100V-277V

Electrical	
Working Voltage	AC 90-305V
Operating Frequency	50/60Hz
Power Factor	>.9
Operating Position	Universal
Operating Temperature	-20C (-4F) to +40C (+104F)

Physical	
MOL	7.56
MOD	2.75
Lens Finish	Clear
Weight (lb.)	0.96

Additional Information	
Additional Info	Replaces HID, CFL, and Incandescent; UL approved for totally enclosed fixtures; For outdoor & indoor use; Emits no UV light / Contains no Mercury (Hg)
Rated For Enclosed Fixture	Yes
IP Rating	IP65
Installation Notes	Not for use in vapor tight fixtures.
Warranty	5 Year Limited - Hi-Pro

Compliance	
Safety Listing	cULus - Certified; cULus - Classified; cULus - Listed
Location Rating	Damp
DLC Approved	No
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
Colorado Status	Lawful for sale
Hawaii Status	Lawful for sale
Nevada Status	Lawful for sale
Vermont Status	Lawful for sale
Washington Status	Lawful for sale
RoHS Compliant	Yes
FCC Compliant	Yes
SDS Sheet	LED_Lamp