

# Eaton TCF20

Catalog Number: TCF20

Eaton Bussmann series TCF fuse, 20 A, 60 Hz, 50 Hz, CF, Black, With indicator, Blade end, Time delay, 10 sec at 500%, 300 kAIC at 600 V, 100 kAIC at 300 Vdc, Glass filled PES, Chassis, 35 mm DIN rail, 600 V, 300 Vdc

## General specifications



<b>Product Name</b>	<b>Catalog Number</b>
Eaton Bussmann series TCF fuse	TCF20
<b>UPC</b>	<b>EAN</b>
051712615013	5027590116954
<b>Product Length/Depth</b>	<b>Product Height</b>
1.88 in	1.75 in
<b>Product Width</b>	<b>Product Weight</b>
0.75 in	0.08 lb
<b>Warranty</b>	<b>Compliances</b>
Not Applicable	CE Marked RoHS Compliant
<b>Certifications</b>	
UL Listed CSA Certified	

## Electrical rating

### Amperage Rating

20 A

### Frequency rating - max

60 Hz

### Frequency rating - min

50 Hz

### Interrupt rating

300 kAIC at 600 Vac

100 kAIC at 300 Vdc

### Response time

10 sec at 500%

### Voltage rating

600 Vac, 300 Vdc

## Physical details

### Color

Black

### Fuse type

Class CF

Time delay

### Material

Glass filled PES

### Number of elements

Dual

### Packaging type

Standard

## General information

### Class

Class CF

### Connection

Blade end

### Fuse indicator

With Indicator

### Mounting method

Chassis

35 mm DIN rail

### Special features

Finger safe

### Used with

TCFH30N, CCP2-3-30CF

## Resources

### Catalogs

[Bussmann series full line catalog 1007, section 01- low voltage branch circuit fuses](#)

### Multimedia

[The Power of Space](#)

[Bussmann series Fuseology](#)

Specifications and datasheets

Eaton Specification Sheet - TCF20

Technical data sheets

TCF20~CUBEFUSE, TCF 20A IND

Technical service bulletins

Datasheet - FNQ-30



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)