



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



S29401 7W Led PAR20 30K 25 Deg Beam

Satco

| | |
|------------------|---|
| Catalog Number | S29401 |
| Manufacturer | Satco |
| Description | 6.5 Watt PAR20 Led Lamp - 3000K - 25 Degree Beam Angle - Medium Base - 120 Volts |
| Weight per unit | 0.2300 (lbs/each) |
| Product Category | Lighting |

Features

| | |
|--------------|--------------------------------|
| average life | 25000 |
| Base | Medium |
| beam angle | 25 |
| lumens | 520 |
| Material | Plastic |
| Shape | PAR20 |
| Warranty | 3 Year Limited - 12 hr per day |

Material, Color, and Finish

| | |
|-------------------|--------|
| color temperature | 3000 |
| Finish | Silver |

Dimensions and Weight

| | |
|------|------|
| Size | 2.99 |
|------|------|

Descriptions

| | |
|------------------------|--|
| Description | 7W LED PAR20 30K 25 DEG BEAM |
| extra long description | SATCO S29401 6.5PAR20/LED/25'/930/1 |
| Long Description | 6.5 Watt PAR20 LED Lamp - 3000K - 25 Degree Beam Angle - Medium Base - 120 Volts |
| Product Type | 6.5PAR20/Led/25'/930/120V |
| Special Features | Lawful for sale in California ; California T24 Compliant ; Yes - Dimmable ; Lens finish: Clear ; Warranty: 3 Year Limited - 12 hours per day ; Wet location rated ; Material: Plastic ; Incandescent Equivalent: 50W ; Enclosed Fixture Rated: Yes ; Operating Temperature: -20C (-4F) to a maximum of +45C (+113F) |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Satco |
| GTIN | 00045923294013 |
| Manufacturers Part Number | S29401 |
| UPC | 045923294013 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description LED PAR SHAPE LAMPS

Type LED PAR

Packaging

Carton 1

Weight 0.1

Weight Per each 0.23

Uses, Certifications, and Standards

Operating Temperature -20C (-4F) to a maximum of +45C (+113F)

standard cULus