



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



TMC10402 4" AI CBL Gland (3.5-4.02)

Crouse-Hinds

Catalog Number	TMC10402
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series TMC Cable Gland, Metal-Clad, Teck Corrugated or Interlocked Steel, or Aluminum, Armoured, Aluminum, Outer Sheath: 3.58-4.28", General Purpose, 4" NPT, Armor Range: 3.50-4.02"
Weight per unit	5.9 (lbs/each)
Product Category	BX, MC, Armored Cable Fittings

Features

dimensions	7.1300 IN X 5.8800 IN X 5.8800 IN
Material	EPDM RUBBER

Dimensions and Weight

Size	3-1/2 in
------	----------

Descriptions

Description	4" AL CBL GLAND (3.5-4.02)
extra long description	CRS-H TMC10402 4 AL FT MC CAB ARMOR
Features	For use with metal-clad cable, TECK corrugated cable or interlocked steel or aluminum cable, Crouse-Hinds series TMC cable glands provide a means for terminating at junction boxes, control centers, panelboards and enclosures for motor control and electrical distribution equipment. TMC cable glands form a mechanical watertight connection and may installed in Class I, Division 2 locations provided there are no arcing and sparking risks in accordance with NEC501.10B.
Long Description	Eaton Crouse-Hinds series TMC cable gland, Metal-clad, TECK corrugated or interlocked steel, or aluminum, Armoured, Aluminum, Outer sheath: 3.58-4.28", General purpose, 4" NPT, Armor range: 3.50-4.02"
Product Type	4 AI FT MC Cab Armor Od 3.50-4.02

Manufacturer Information

Brand	Crouse-Hinds
GTIN	00782274414645
Manufacturers Part Number	TMC10402
UPC	782274414645

Taxonomies, Classifications, and Categories

Category Description	CORD CONNECTORS & CORD GRIPS
Type	Cable gland



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	5.9

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Industrial Facilities/Factories - Other
Enclosure standard	IP56 UL 514B, UL 886
Temperature Rating	-25 To 60 Deg C