



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



TMC3112 1" Cord Grips *Crouse-Hinds*

Catalog Number	TMC3112
Manufacturer	Crouse-Hinds
Description	TMC Armored Cable Gland, Aluminum, 1 In Size, 2.625 In (Gland) Length, -25 °C Operating Temperature, +60 °C Operating Temperature, Grip Connection, Non-Insulated, 0.51 LB/Ea
Weight per unit	0.4800 (lbs/each)
Product Category	BX, MC, Armored Cable Fittings

Features

dimensions	4.0700 IN X 2.0000 IN X 2.0000 IN
------------	-----------------------------------

Material, Color, and Finish

Finish	Nickel Plated
--------	---------------

Descriptions

Description	1" CORD GRIPS
extra long description	CRS-H TMC3112 1 AL FT MC CAB ARMOR
Features	For use with metal-clad cable, TECK corrugated cable or interlocked steel or aluminum cable, Crouse-Hinds series TMC cable glands provide a means for terminating at junction boxes, control centers, panelboards and enclosures for motor control and electrical distribution equipment. TMC cable glands form a mechanical watertight connection and may installed in Class I, Division 2 locations provided there are no arcing and sparking risks in accordance with NEC501.10B.

Manufacturer Information

Brand	Eaton
GTIN	00782274414560
UPC	782274414560

Taxonomies, Classifications, and Categories

Category Description	CORD CONNECTORS & CORD GRIPS
Type	Cable gland

Packaging

Carton	5
Weight Per each	0.48

Uses, Certifications, and Standards

Enclosure	IP56
Temperature Rating	-25 To 60 Deg C