


# Specifications



## Eaton TR5362CDV

Eaton Arrow Hart heavy duty industrial specification grade duplex receptacle, Tamper resistant, auto-grounding, Dual control, #14-10 AWG, 20A, Flush, 125V, Ivory, Brass, Impact-resistant thermoplastic face, PVC body, 5-20R, 2-pole, 3-wire, ,

### General specifications

<b>PRODUCT NAME</b>	Eaton Arrow Hart heavy-duty industrial specification grade duplex receptacle
<b>CATALOG NUMBER</b>	TR5362CDV
<b>UPC</b>	032664744655
<b>PRODUCT LENGTH/DEPTH</b>	1.3 in
<b>PRODUCT HEIGHT</b>	4.19 in
<b>PRODUCT WIDTH</b>	0.84 in
<b>PRODUCT WEIGHT</b>	0.22 lb
<b>CERTIFICATIONS</b>	cULus Listed

Product specifications	
DEVICE TYPE	Receptacle
TYPE	Dual control
AMPERAGE RATING	20A
VOLTAGE RATING	125V
CONTACT MATERIAL	Brass
FEATURES	Tamper resistant Auto-grounding Dual-controlled
APPLICATION	Industrial
DEVICE GRADE	Construction
WIRING METHOD	Back and side
NUMBER OF WIRES	Three-wire
MOUNTING METHOD	Flush
NUMBER OF POLES	Two-pole
STYLE TYPE	Standard
COLOR	Ivory
CONNECTION TYPE	Screw
ALLOWABLE WIRE SIZE	#14-10 AWG
NEMA CONFIGURATION	5-20R
TORQUE RATING	14 lbf-inch
DESIGN TYPE	Straight blade
FACE/BODY MATERIAL	PVC Body Impact-resistant thermoplastic face
RECEPTACLE TYPE	Duplex

Resources	
BROCHURES	<a href="#">Spec grade receptacles brochure</a>
	<a href="#">Controlled receptacles sell sheet</a>
MULTIMEDIA	<a href="#">Residential straight blade receptacles</a>
SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - TR5362CDV</a>

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.


Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



# Specifications



## Eaton TR5362CDV

Eaton Arrow Hart heavy duty industrial specification grade duplex receptacle, Tamper resistant, auto-grounding, Dual control, #14-10 AWG, 20A, Flush, 125V, Ivory, Brass, Impact-resistant thermoplastic face, PVC body, 5-20R, 2-pole, 3-wire, ,

### General specifications

PRODUCT NAME	Eaton Arrow Hart heavy-duty industrial specification grade duplex receptacle
CATALOG NUMBER	TR5362CDV
UPC	032664744655
PRODUCT LENGTH/DEPTH	1.3 in
PRODUCT HEIGHT	4.19 in
PRODUCT WIDTH	0.84 in
PRODUCT WEIGHT	0.22 lb
CERTIFICATIONS	cULus Listed

Product specifications	
DEVICE TYPE	Receptacle
TYPE	Dual control
AMPERAGE RATING	20A
VOLTAGE RATING	125V
CONTACT MATERIAL	Brass
FEATURES	Tamper resistant Auto-grounding Dual-controlled
APPLICATION	Industrial
DEVICE GRADE	Construction
WIRING METHOD	Back and side
NUMBER OF WIRES	Three-wire
MOUNTING METHOD	Flush
NUMBER OF POLES	Two-pole
STYLE TYPE	Standard
COLOR	Ivory
CONNECTION TYPE	Screw
ALLOWABLE WIRE SIZE	#14-10 AWG
NEMA CONFIGURATION	5-20R
TORQUE RATING	14 lbf-inch
DESIGN TYPE	Straight blade
FACE/BODY MATERIAL	PVC Body Impact-resistant thermoplastic face
RECEPTACLE TYPE	Duplex

Resources	
BROCHURES	<a href="#">Spec grade receptacles brochure</a>
	<a href="#">Controlled receptacles sell sheet</a>
MULTIMEDIA	<a href="#">Residential straight blade receptacles</a>
SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - TR5362CDV</a>

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



**Eaton Corporation plc**

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights  
Reserved.

Eaton is a registered trademark.

All other trademarks are property of  
their respective owners.

Follow us on social media to get the latest  
product and support information.

