




MILBANK
ENERGY AT WORK

U4184-X




Catalog Number	U4184-X	Enclosure	G90 Galvanized Steel with Powder Coat Finish
Marketing Product Description	7 Terminal Ringless Large Closing Plate Lever Bypass 200 Ampere Side Bussed	Jaw Quantity	7 Terminal
UPC	784572174351	Bypass Type	Lever Bypass
Length (IN)	6	Number of Meter Positions	1 Position
Width (IN)	18	Equipment Ground	Ground Lug
Height (IN)	19.25	Hub Opening	Large Closing Plate
Brand Name	Milbank	Line Side Wire Range	6 AWG - 350 kcmil
Type	Ringless Meter Socket	Load Side Wire Range	6 AWG - 350 kcmil
Application	Meter Socket	Number Of Receptacles	0
Standard	UL Listed;Type 3R		
Voltage Rating	600 Volts Alternating Current		
Amperage Rating	200 Continuous Ampere		
Phase	3 Phase		
Frequency Rating	60 Hertz		
Size	6L x 18W x 19.25H		
Number Of Cutouts	0		
Cutout Size	No Main Breaker		
Cable Entry	Overhead and Underground and Side Wireway		
Terminal	Lay in		
Insulation	Glass Polyester		
Mounting	Surface Mount		

Please consult serving utility for their requirements prior to ordering or installing, as specifications and approvals vary by utility and may require local electrical inspector approval. All installations must be installed by a licensed electrician and must comply with all national and local codes, laws and regulations. Milbank reserves the right to make changes in specifications and features shown without notice or obligation.



MILBANK
ENERGY AT WORK

U4184-X



Catalog Number	U4184-X
Marketing Product Description	7 Terminal Ringless Large Closing Plate Lever Bypass 200 Ampere Side Bussed
UPC	784572174351
Length (IN)	6
Width (IN)	18
Height (IN)	19.25
Brand Name	Milbank
Type	Ringless Meter Socket
Application	Meter Socket
Standard	UL Listed;Type 3R
Voltage Rating	600 Volts Alternating Current
Amperage Rating	200 Continuous Ampere
Phase	3 Phase
Frequency Rating	60 Hertz
Size	6L x 18W x 19.25H
Number Of Cutouts	0
Cutout Size	No Main Breaker
Cable Entry	Overhead and Underground and Side Wireway
Terminal	Lay in
Insulation	Glass Polyester
Mounting	Surface Mount

Enclosure	G90 Galvanized Steel with Powder Coat Finish
Jaw Quantity	7 Terminal
Bypass Type	Lever Bypass
Number of Meter Positions	1 Position
Equipment Ground	Ground Lug
Hub Opening	Large Closing Plate
Line Side Wire Range	6 AWG - 350 kcmil
Load Side Wire Range	6 AWG - 350 kcmil
Number Of Receptacles	0

Please consult serving utility for their requirements prior to ordering or installing, as specifications and approvals vary by utility and may require local electrical inspector approval. All installations must be installed by a licensed electrician and must comply with all national and local codes, laws and regulations. Milbank reserves the right to make changes in specifications and features shown without notice or obligation.