




MILBANK
ENERGY AT WORK

U7040-XL-TG



| | |
|-------------------------------|--|
| Catalog Number | U7040-XL-TG |
| Marketing Product Description | 4 Terminal Ringless Small Closing Plate Triplex Ground |
| UPC | 784572140356 |
| Length (IN) | 4.125 |
| Width (IN) | 11 |
| Height (IN) | 14.563 |
| Brand Name | Milbank |
| Type | Ringless Meter Socket |
| Application | Meter Socket |
| Standard | UL Listed;Type 3R |
| Voltage Rating | 600 Volts Alternating Current |
| Amperage Rating | 200 Continuous Ampere |
| Phase | 1 Phase |
| Frequency Rating | 60 Hertz |
| Size | 4.125L x 11W x 14.563H |
| Number Of Cutouts | 0 |
| Cutout Size | No Main Breaker |
| Cable Entry | Overhead or Underground |
| Terminal | Lay in |
| Insulation | Glass Polyester |
| Mounting | Surface Mount |
| Enclosure | G90 Galvanized Steel with Powder Coat Finish |


| | |
|---------------------------|---------------------|
| Jaw Quantity | 4 Terminal |
| Bypass Type | No Bypass |
| Number of Meter Positions | 1 Position |
| Equipment Ground | Triplex Ground |
| Hub Opening | Small Closing Plate |
| Line Side Wire Range | 6 AWG - 350 kcmil |
| Load Side Wire Range | 6 AWG - 350 kcmil |
| Number Branch Circuits | 0 |
| Number Of Receptacles | 0 |

Please consult serving utility for their requirements prior to ordering or installing, as specifications and approvals vary by utility and may require local electrical inspector approval. All installations must be installed by a licensed electrician and must comply with all national and local codes, laws and regulations. Milbank reserves the right to make changes in specifications and features shown without notice or obligation.



MILBANK
ENERGY AT WORK

U7040-XL-TG



| | |
|-------------------------------|--|
| Catalog Number | U7040-XL-TG |
| Marketing Product Description | 4 Terminal Ringless Small Closing Plate Triplex Ground |
| UPC | 784572140356 |
| Length (IN) | 4.125 |
| Width (IN) | 11 |
| Height (IN) | 14.563 |
| Brand Name | Milbank |
| Type | Ringless Meter Socket |
| Application | Meter Socket |
| Standard | UL Listed;Type 3R |
| Voltage Rating | 600 Volts Alternating Current |
| Amperage Rating | 200 Continuous Ampere |
| Phase | 1 Phase |
| Frequency Rating | 60 Hertz |
| Size | 4.125L x 11W x 14.563H |
| Number Of Cutouts | 0 |
| Cutout Size | No Main Breaker |
| Cable Entry | Overhead or Underground |
| Terminal | Lay in |
| Insulation | Glass Polyester |
| Mounting | Surface Mount |
| Enclosure | G90 Galvanized Steel with Powder Coat Finish |

| | |
|---------------------------|---------------------|
| Jaw Quantity | 4 Terminal |
| Bypass Type | No Bypass |
| Number of Meter Positions | 1 Position |
| Equipment Ground | Triplex Ground |
| Hub Opening | Small Closing Plate |
| Line Side Wire Range | 6 AWG - 350 kcmil |
| Load Side Wire Range | 6 AWG - 350 kcmil |
| Number Branch Circuits | 0 |
| Number Of Receptacles | 0 |

Please consult serving utility for their requirements prior to ordering or installing, as specifications and approvals vary by utility and may require local electrical inspector approval. All installations must be installed by a licensed electrician and must comply with all national and local codes, laws and regulations. Milbank reserves the right to make changes in specifications and features shown without notice or obligation.