



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



T2535163S T2535163S *Acme Electric*

Catalog Number	T2535163S
Manufacturer	Acme Electric
Description	Low Voltage Distribution Transformer - Single Phase, 240X480 - 120/240V, 10kva
Weight per unit	127.0 (lbs/each)
Product Category	Single Phase Non Ventilated to

Features

Fuse Rating	Primary: 60 AMP For 240 V, 30 AMP For 480 V, Secondary: 110 AMP For 120 V
pallet quantity	6
Primary Voltage	240 X 480
product category	Dry Type Distribution Transformer
Secondary Voltage	120/240

Dimensions and Weight

Height	15.19
Length	10.84
Width	13.5

Descriptions

Construction	ENCAPSULATED
Description	T2535163S
extra long description	ACME T2535163S TFMR 1PH 10KVA 240X4
Long Description	Low Voltage Distribution Transformer - Single Phase, 240X480 - 120/240V, 10kVA
Product Type	Dry Type Distribution Transformer
Special Features	Encapsulated core and coil; Shielded for cleaner power; Encapsulated and completely enclosed design electrical grade silica and resin compounds completely enclose the core and coil to seal out all moisture and air, UL type 3R enclosure for indoor or outdoor service, encapsulation eliminates corrosion and insulation deterioration; Quiet operation with sound levels well below NEMA standards; 10-year limited warranty

Manufacturer Information

Brand	ACME ELECTRIC
GTIN	00047503734100
Manufacturers Part Number	T2535163S
UPC	047503734100



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Type Distribution Transformer

Packaging

Carton 1

Weight Per each 127

Uses, Certifications, and Standards

Enclosure NEMA 3R Steel

Mounting WALL

standard UL 506, UL File Number E79947V1, UL Control Number 50B8, UL
Insulation Number H3221, CSA Certified, OSHA Compliant, ANSI,
IEEE

Temperature Rating 115 DEG C Rise