

Project:	Type:	Prepared By:	Date:
-----------------	--------------	---------------------	--------------



Features and Benefits

- Direct Replacement for Fluorescent Lamps: F32T8/32W, F32T8/30W, F32T8/28W, F32T8/25W
- Easy to install plug and play that requires no rewiring, no tools, no instructions
- 50,000 hour Lifespan
- Rated for use in enclosed and open fixtures in dry or damp locations
- Diffused frosted lens will maintain the same light quality over time
- Compatible with most instant start electronic T8 ballasts, Please check Compatibility List
- Approximately 40% more efficient than fluorescent T8 lamps
- Instant on full brightness
- Environmentally friendly, no mercury used
- NSF Listed: NSF/ANSI Standard 2 - Food Equipment - Splash Zone (Not for Direct Food Zone without additional fixture considerations)
- Compatible with RAB specified 0-10V dimming system

Technical Specifications		
Performance	Nominal Length:	Power Factor:
Product Type: Linear	4 ft	Ballast Dependent
Input Wattage: 14W	Finish: Frosted	Operating Temperature: -20°C to 45°C (-4°F to 113°F)
Lumens: 2,200lm	For Use Outdoors in Open Fixtures: No	Dimming: Yes with 0-10V dimmer & plus; ballast. See Dimmer Compatibility List.
Efficacy: 157lm/W	LED Characteristics	Input Voltage: Ballast Dependent
L70 Lifespan: 50,000 Hours	Color Temperature: 4000K Cool White	Operating Frequency: Ballast Dependent
Wattage Equivalency: 32W Fluorescent	Color Accuracy (CRI): 80 CRI	Input Current @ 120V: Ballast Dependent
Construction	Installation	Input Current @ 277V: Ballast Dependent
Material: Coated Glass	Base Type: G13	Flicker: Ballast Dependent
Bulb Shape: T8	Installation Type: Type A, Plug and Play	
	Electrical	
	THD: ≤25%	

Technical Specifications (continued)

Other

Warranty:

RAB warrants that our LED products will be free from defects in materials and workmanship for a period of five (5) years from the date of delivery to the end user, including coverage of light output, color stability, driver performance and fixture finish. RAB's warranty is subject to all terms and conditions found at rablighting.com/warranty.

Compliance

UL Listed:

Yes

NSF Listed:

Meets NSF/ANSI standards for use in Food Zone (non-contact), Splash, and Non-Food Zones. Tube guard required in open fixtures.

Certification Model Number:

T10017

California Energy Commission (CEC) Status:

Lawful for Sales in California

Application:

Suitable for damp locations and totally enclosed fixtures.

DLC Listed:

This product is on the Design Lights Consortium (DLC) Qualified Products List and is eligible for rebates from DLC Member Utilities. Designed to meet DLC 5.1 requirements.

DLC Product Code: PL5P4N7GYLU5

Optical

Beam Angle:

180°


Ballast Performance

	0.78BF	0.88BF	1.88BF
Lumens	1750	2200	3000
System Power (W)	13	16	22.3


Case and Pallet Dimensions

	QTY	LENGTH (in)	WIDTH (in)	HEIGHT (in)
CASE	25	49.4	7.7	8
PALLET	625	43.3	40.6	51.2

Wiring Diagram



Dimension



Light Distribution

