



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



UNF305SA 1" Alu Female Union

Crouse-Hinds

Catalog Number	UNF305SA
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series Unf Union, Rigid/Imc, Female, Copper-Free Aluminum, Group B Rated, 1"
Weight per unit	0.2700 (lbs/each)
Product Category	Aluminum

Features

connection	Threaded
dimensions	2.0900 IN X 2.0300 IN X 2.0300 IN

Descriptions

Description	1" ALU FEMALE UNION
extra long description	CRS-H UNF305 SA 1 NPT FEMALE AL UNF
Features	Crouse-Hinds series explosionproof unions are installed in rigid/IMC conduit systems to connect conduit to conduit, a conduit fitting, junction box or device enclosure. Expansion unions are also available, which allow for expansion and contraction of conduit and compensate for conduit cut too short. Available in a variety of materials, including stainless steel, to suit customer preferences. Explosionproof elbows allow for a 90° change in direction to the conduit run, or when terminating at a box or fit
Long Description	Eaton Crouse-Hinds series UNF union, Rigid/IMC, Female, Copper-free aluminum, Group B rated, 1"
Product Type	1 NPT Female Al Unf Union
Special Features	1-7/8 In Diameter X 2 In Length

Manufacturer Information

Brand	EATON CROUSE-HINDS SERIES
GTIN	00782274101842
Manufacturers Part Number	UNF305 SA
UPC	782274101842

Taxonomies, Classifications, and Categories

Category Description	HAZARDOUS LOCATION FITTINGS
Type	Union

Packaging

Carton	1
Package	5
Weight Per each	0.27



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Industrial Facilities/Factories - Other
Enclosure	Class I Div 1 2 Group B C D, Class II Div 1 Group E F G, Class II Div 2
.....	Group F G, Class III
standard	UL 886, CSA C22.2