## Eaton TCF40

Eaton Bussmann Series Class CF fuse, TCF, time-delay, dual-element current limiting cube fuse, 40 A, indicating fuse, interrupting rating of 100 kA at 300 Vdc and 300 kA at 600 Vac

General specifications		
PRODUCT NAME	Eaton Bussmann series TCF fuse	
CATALOG NUMBER	TCF40	
UPC	051712615051	
EAN	5027590116992	
PRODUCT LENGTH/DEPTH	2.13 in	
PRODUCT HEIGHT	1.9 in	
PRODUCT WIDTH	1 in	
PRODUCT WEIGHT	0.17 lb	
WARRANTY	Not Applicable	
COMPLIANCES	CE Marked RoHS Compliant	
CERTIFICATIONS	UL Listed CSA Certified	



<b>Electrical rating</b>		
AMPERAGE RATING	40 A	
FREQUENCY RATING - MAX	60 Hz	
FREQUENCY RATING - MIN	50 Hz	
INTERRUPT RATING	100 kAIC at 300 Vdc 300 kAIC at 600 Vac	
RESPONSE TIME	10 sec at 500%	
VOLTAGE RATING	600 Vac, 300 Vdc	

Physical details	
COLOR	Black
FUSE TYPE	Class CF Time delay
MATERIAL	Glass filled PES
NUMBER OF ELEMENTS	Dual
PACKAGING TYPE	Standard

Resources	
	Bussmann Full Line Catalog
CATALOGS	Low Voltage Branch Circuit Fuse Chapter

General information	
CLASS	Class CF
CONNECTION	Blade end
FUSE INDICATOR	With Indicator

MOUNTING METHOD	Chassis 35 mm DIN rail	COMPLIANCE INFORMATION	RoHS Search Tool
SPECIAL FEATURES	Finger safe	MULTIMEDIA	Bussmann series Fuseology
USED WITH	TCFH60N, CCP2-3-60CF		The Power of Space
		TECHNICAL DATA SHEETS	Bussmann series UL Class CF CUBEFuse data sheet no. 9000

## **PROJECT NAME:**

**PROJECT NUMBER:** 

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

