

## DESCRIPTION

The ALL-PRO™ Vapor tight Floodlight provides an indoor/outdoor solution in applications where lighting fixture protection is required. The fixture is wet location rated and vapor tight to protect against dust and moisture. Perfect for patios, garages, storage, and industrial areas.

<b>Catalog #</b>		<b>Type</b>
<b>Project</b>		
<b>Comments</b>		<b>Date</b>
<b>Prepared by</b>		

## SPECIFICATION FEATURES

### Construction

- Durable die-cast aluminum housing and guard provides protection against vandalism
- Vapor tight protects against dust and moisture
- Suitable for wall or ceiling mounting application
- Removable glass lens
- 1/2" conduit openings on top and sides

### Electrical

- Electrical operating voltage 120VAC 50/60HZ
- Fixture operating temperature range from -20°C to 40°C
- cULus listed for wet locations
- Minimum 125°C supply conductors

### Optics

- 100W (maximum) incandescent bulb (sold separately)

### Warranty


- 2 year limited warranty




## VAPOR TIGHT FLOODLIGHT

## DIMENSIONS

Top View



Side View



## ORDERING INFORMATION

Sample Number: VT100G



**Application**

VT = Vapor Tight

**Series**

100 = 100Watts

## CERTIFICATION DATA

cULus Wet Location Listed

## TECHNICAL DATA

-20°C to 40°C Temperature Rating

## TECHNICAL INFORMATION

Model Number	Description	Voltage (V)	Power (W)	Lamp Lumens	Color Temperature (K)	CRI
VT100G	ALL-PRO Vapor Tight Floodlight	120V	100W	1600	2700K	100

## DESCRIPTION

The ALL-PRO™ Vapor tight Floodlight provides an indoor/outdoor solution in applications where lighting fixture protection is required. The fixture is wet location rated and vapor tight to protect against dust and moisture. Perfect for patios, garages, storage, and industrial areas.

<b>Catalog #</b>		<b>Type</b>
<b>Project</b>		
<b>Comments</b>		<b>Date</b>
<b>Prepared by</b>		

## SPECIFICATION FEATURES

### Construction

- Durable die-cast aluminum housing and guard provides protection against vandalism
- Vapor tight protects against dust and moisture
- Suitable for wall or ceiling mounting application
- Removable glass lens
- 1/2" conduit openings on top and sides

### Electrical

- Electrical operating voltage 120VAC 50/60HZ
- Fixture operating temperature range from -20°C to 40°C
- cULus listed for wet locations
- Minimum 125°C supply conductors

### Optics

- 100W (maximum) incandescent bulb (sold separately)


### Warranty

- 2 year limited warranty




## VAPOR TIGHT FLOODLIGHT

## DIMENSIONS



## ORDERING INFORMATION

Sample Number: VT100G



### CERTIFICATION DATA

cULus Wet Location Listed

### TECHNICAL DATA

-20°C to 40°C Temperature Rating

## TECHNICAL INFORMATION

Model Number	Description	Voltage (V)	Power (W)	Lamp Lumens	Color Temperature (K)	CRI
VT100G	ALL-PRO Vapor Tight Floodlight	120V	100W	1600	2700K	100