



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



WP832 20A 125V 5-20P 2W3P WP Plug (05-.625)

Crouse-Hinds

Catalog Number	WP832
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series WP Plug, 20A, Two-Wire, Three-Pole, Copper-Free Aluminum, 5-20P, 0.500-0.625" Cord Diameter, 125 Vac
Weight per unit	N/A
Product Category	Plugs, Connectors, Inlets, Out

Features

amperage rating	20
Cord Type	0.500 To 0.625 In
dimensions	3.5000 IN X 2.5000 IN X 2.5000 IN
Material	Copper-Free Aluminum
Poles	3
Voltage Rating	125 VAC

Descriptions

Description	20A 125V 5-20P 2W3P WP PLUG (05-.625)
extra long description	CRS-H WP832 20A 125V 2 WIRE 3 POLE
Features	Crouse-Hinds series FS and FD device boxes are installed in non-hazardous area conduit systems to accommodate wiring devices, act as pull boxes or provide openings for taps and splices. They are suitable for use in wet locations when used with gasketed covers. FS and FD device boxes are available in two box depths with a wide variety of gang configurations, hub configurations and hub sizes. They are manufactured in cast iron, aluminum, stainless steel and malleable iron. Malleable iron boxes are also a
Long Description	Eaton Crouse-Hinds series WP plug, 20A, Two-wire, three-pole, Copper-free aluminum, 5-20P, 0.500-0.625" cord diameter, 125 Vac
Product Type	20A 125V 2 Wire 3 Pole WP PLG
Special Features	Weatherproof

Manufacturer Information

Brand	Crouse-Hinds
GTIN	00782274085333
Manufacturers Part Number	WP832
UPC	782274085333



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description FS BOXES AND COVERS

Type PLUG

Packaging

Carton 1

Weight Per each 0

Uses, Certifications, and Standards

Application Ind Facilities & Factories - Industrial Facilities/Factories - Other

standard UL 498, UL 514A, CSA C22.2