

# Eaton XJG108 SA

Catalog Number: XJG108 SA

Eaton Crouse-Hinds series XJG expansion coupling, Rigid/IMC, Copper-free aluminum, 8" maximum conduit movement, 4" trade size

## General specifications



Product Name	Catalog Number
Eaton Crouse-Hinds series XJG expansion coupling	XJG108 SA
	UPC
	782274916095
Product Length/Depth	Product Height
13.81 in	6.62 in
Product Width	Product Weight
6.62 in	10.55 lb

Photo is representative

## Certifications and compliances

### Area classification

Ordinary/Non-Hazardous Locations

### Standards type

NEC/CEC

## Product specifications

### Type

Expansion

### Conduit type

Rigid/IMC

### Trade size

4"

### Conduit movement - max

8"

### Material

Copper-free aluminum

## Resources

### Brochures

[Crouse-Hinds series Conduit Expansion/Deflection Couplings brochure](#)

### Catalogs

[Crouse-Hinds series XJG Conduit Expansion Couplings for Rigid/IMC catalog page](#)

### Certification reports

[XJG Conduit Expansion Couplings for EMT and Rigid/IMC UL certification](#)

[XJG Conduit Expansion Couplings for EMT and Rigid/IMC Canadian certification](#)

### Installation instructions

[IF 343 - Type XJ Expansion Joints](#)

[IF 1508 - Assembly-Free XJG](#)

### Specifications and datasheets

[Expansion and Deflection Couplings](#)

[Eaton Specification Sheet - XJG108 SA](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton XJG108 SA

Catalog Number: XJG108 SA

Eaton Crouse-Hinds series XJG expansion coupling, Rigid/IMC, Copper-free aluminum, 8" maximum conduit movement, 4" trade size

## General specifications



<b>Product Name</b>	<b>Catalog Number</b>
Eaton Crouse-Hinds series XJG expansion coupling	XJG108 SA
	UPC
	782274916095
<b>Product Length/Depth</b>	<b>Product Height</b>
13.81 in	6.62 in
<b>Product Width</b>	<b>Product Weight</b>
6.62 in	10.55 lb

Photo is representative

## Certifications and compliances

### Area classification

Ordinary/Non-Hazardous Locations

### Standards type

NEC/CEC

## Product specifications

### Type

Expansion

### Conduit type

Rigid/IMC

### Trade size

4"

### Conduit movement - max

8"

### Material

Copper-free aluminum

## Resources

### Brochures

[Crouse-Hinds series Conduit Expansion/Deflection Couplings brochure](#)

### Catalogs

[Crouse-Hinds series XJG Conduit Expansion Couplings for Rigid/IMC catalog page](#)

### Certification reports

[XJG Conduit Expansion Couplings for EMT and Rigid/IMC UL certification](#)

[XJG Conduit Expansion Couplings for EMT and Rigid/IMC Canadian certification](#)

### Installation instructions

[IF 343 - Type XJ Expansion Joints](#)

[IF 1508 - Assembly-Free XJG](#)

### Specifications and datasheets

[Expansion and Deflection Couplings](#)

[Eaton Specification Sheet - XJG108 SA](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)