

Specifications

Eaton XJG108 SA

Eaton Crouse-Hinds series XJG expansion coupling, Rigid/IMC, Copper-free aluminum, 8" maximum conduit movement, 4" trade size



Photo is representative

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series XJG expansion coupling
CATALOG NUMBER	XJG108 SA
UPC	782274916095
PRODUCT LENGTH/DEPTH	13.81 in
PRODUCT HEIGHT	6.62 in
PRODUCT WIDTH	6.62 in
PRODUCT WEIGHT	10.55 lb



Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous
----------------------------	------------------------

Product specifications

TYPE	Expansion
-------------	-----------

	Locations
STANDARDS TYPE	NEC/CEC

CONDUIT TYPE	Rigid/IMC
TRADE SIZE	4"
CONDUIT MOVEMENT - MAX	8"
MATERIAL	Copper-free aluminum

Resources

BROCHURES	Crouse-Hinds series Conduit Expansion/Deflection Couplings brochure
CATALOGS	Crouse-Hinds series XJG Conduit Expansion Couplings for Rigid/IMC catalog page
CERTIFICATION REPORTS	XJG Conduit Expansion Couplings for EMT and Rigid/IMC Canadian certification XJG Conduit Expansion Couplings for EMT and Rigid/IMC UL certification
INSTALLATION INSTRUCTIONS	IF 1508 - Assembly-Free XJG IF 343 - Type XJ Expansion Joints
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - XJG108 SA Expansion and Deflection Couplings

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.



Specifications

Eaton XJG108 SA

Eaton Crouse-Hinds series XJG expansion coupling, Rigid/IMC, Copper-free aluminum, 8" maximum conduit movement, 4" trade size



Photo is representative

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series XJG expansion coupling
CATALOG NUMBER	XJG108 SA
UPC	782274916095
PRODUCT LENGTH/DEPTH	13.81 in
PRODUCT HEIGHT	6.62 in
PRODUCT WIDTH	6.62 in
PRODUCT WEIGHT	10.55 lb



Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous
----------------------------	------------------------

Product specifications

TYPE	Expansion
-------------	-----------

	Locations
STANDARDS TYPE	NEC/CEC

CONDUIT TYPE	Rigid/IMC
TRADE SIZE	4"
CONDUIT MOVEMENT - MAX	8"
MATERIAL	Copper-free aluminum

Resources

BROCHURES	Crouse-Hinds series Conduit Expansion/Deflection Couplings brochure
CATALOGS	Crouse-Hinds series XJG Conduit Expansion Couplings for Rigid/IMC catalog page
CERTIFICATION REPORTS	XJG Conduit Expansion Couplings for EMT and Rigid/IMC Canadian certification XJG Conduit Expansion Couplings for EMT and Rigid/IMC UL certification
INSTALLATION INSTRUCTIONS	IF 1508 - Assembly-Free XJG IF 343 - Type XJ Expansion Joints
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - XJG108 SA Expansion and Deflection Couplings

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

