

NEER™ Zinc Offset Nipples and Three Piece Couplings

NEC/CEC:
Listed for Ordinary Locations

NEC:
Listed for Ordinary Locations

RN: 3/4" Offset

Applications

- To provide an offset connection between two outlet boxes or enclosures.

Material/Finish

- Zinc diecast

NEC/CEC Certifications and Compliances

- UL Standard: 514B
- UL Listed: E32539
- CSA Standard: C22.2 No. 18.3
- CSA Certified: 70872
- NEMA: FB-1



RN-50

TPC: Three Piece

Applications

- Provides threaded coupling between lengths of rigid conduit and IMC conduit elbows, where neither can be rotated.

Material/Finish

- Malleable iron/zinc plated


NEC Certifications and Compliances

- UL Standard: 514B
- UL Listed: E163167
- NEMA: FB-1



TPC - 50

Illustrated Dimensions



Trade Size (Inches)	Dimensions in Millimeters (Inches)			Catalog Number
	Body Length	Maximum Diameter		
1/2	62.2 (2.45)	23.9 (0.94)		RN-50
3/4	66.0 (2.60)	29.2 (1.15)		RN-75
1	70.1 (2.76)	35.6 (1.40)		RN-100
1-1/4	73.7 (2.90)	46.7 (1.84)		RN-125
1-1/2	77.5 (3.05)	52.3 (2.06)		RN-150
2	82.0 (3.23)	67.6 (2.66)		RN-200

Trade Size (Inches)	Dimensions in Millimeters (Inches)			Catalog Number
	A	B	C	
1/2	34.5 (1.36)	33.0 (1.30)	30.5 (1.20)	TPC-50
3/4	41.4 (1.63)	39.9 (1.57)	33.0 (1.30)	TPC-75
1	43.2 (1.70)	54.1 (2.13)	47.8 (1.88)	TPC-100
1-1/4	53.8 (2.12)	62.0 (2.44)	54.4 (2.14)	TPC-125
1-1/2	50.8 (2.00)	73.4 (2.89)	66.3 (2.61)	TPC-150
2	60.5 (2.38)	86.6 (3.41)	79.5 (3.13)	TPC-200
2 - 1/2	64.5 (2.54)	102.4 (4.03)	99.3 (3.91)	TPC-250
3	65.0 (2.56)	16.8 (4.60)	110.7 (4.36)	TPC-300
3 - 1/2	64.5 (2.54)	17.1 (4.61)	111.0 (4.37)	TPC-350
4	100.1 (3.94)	42.5 (5.61)	129.5 (5.10)	TPC-400

NEER™ Zinc Offset Nipples and Three Piece Couplings

NEC/CEC:
Listed for Ordinary Locations

NEC:
Listed for Ordinary Locations

RN: 3/4" Offset

Applications

- To provide an offset connection between two outlet boxes or enclosures.

Material/Finish

- Zinc diecast

NEC/CEC Certifications and Compliances

- UL Standard: 514B
- UL Listed: E32539
- CSA Standard: C22.2 No. 18.3
- CSA Certified: 70872
- NEMA: FB-1



RN-50

TPC: Three Piece

Applications

- Provides threaded coupling between lengths of rigid conduit and IMC conduit elbows, where neither can be rotated.

Material/Finish

- Malleable iron/zinc plated


NEC Certifications and Compliances

- UL Standard: 514B
- UL Listed: E163167
- NEMA: FB-1



TPC - 50

Illustrated Dimensions



Trade Size (Inches)	Dimensions in Millimeters (Inches)			Catalog Number
	Body Length	Maximum Diameter		
1/2	62.2 (2.45)	23.9 (0.94)		RN-50
3/4	66.0 (2.60)	29.2 (1.15)		RN-75
1	70.1 (2.76)	35.6 (1.40)		RN-100
1-1/4	73.7 (2.90)	46.7 (1.84)		RN-125
1-1/2	77.5 (3.05)	52.3 (2.06)		RN-150
2	82.0 (3.23)	67.6 (2.66)		RN-200

Trade Size (Inches)	Dimensions in Millimeters (Inches)			Catalog Number
	A	B	C	
1/2	34.5 (1.36)	33.0 (1.30)	30.5 (1.20)	TPC-50
3/4	41.4 (1.63)	39.9 (1.57)	33.0 (1.30)	TPC-75
1	43.2 (1.70)	54.1 (2.13)	47.8 (1.88)	TPC-100
1-1/4	53.8 (2.12)	62.0 (2.44)	54.4 (2.14)	TPC-125
1-1/2	50.8 (2.00)	73.4 (2.89)	66.3 (2.61)	TPC-150
2	60.5 (2.38)	86.6 (3.41)	79.5 (3.13)	TPC-200
2 - 1/2	64.5 (2.54)	102.4 (4.03)	99.3 (3.91)	TPC-250
3	65.0 (2.56)	16.8 (4.60)	110.7 (4.36)	TPC-300
3 - 1/2	64.5 (2.54)	17.1 (4.61)	111.0 (4.37)	TPC-350
4	100.1 (3.94)	42.5 (5.61)	129.5 (5.10)	TPC-400