



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



YA25A7 1/0AWG Alcu 2H Lug *Burndy LLC*

Catalog Number	YA25A7
Manufacturer	Burndy LLC
Description	1/0 Awg, Al Terminal, Two Hole, 1/2" Stud Size, 1-3/4" Hole Spacing, AL9CU, Internal Chamfer, Tin Plated, Prefilled Penetrox , End Cap, UI/Csa, 90 C, Up to 35KV, Tan Color Code, 296 Die Index.
Weight per unit	0.0900 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Die Index	296
Material	Aluminum
Voltage Rating	35

Material, Color, and Finish

Color Code	TAN
------------	-----

Descriptions

Description	1/0AWG ALCU 2H LUG
extra long description	BUR YA25A7 1/0 AL 2-HOLE 1/2
Long Description	1/0 AWG, AL Terminal, Two Hole, 1/2" Stud Size, 1-3/4" Hole Spacing, AL9CU, Internal Chamfer, Tin Plated, Prefilled PENETROX , End Cap, UL/CSA, 90 C, Up to 35kV, Tan Color Code, 296 Die Index.
Product Type	Terminal
Special Features	Features: For Aluminum And Copper Conductors, 2-Hole And 4-Hole Designs UI Listed 90 DEG C, 600 V To 35 KV, Type Ya-A 2- And 4-Hole Pads Inhibit Connector Rotation And Increase Area Contact, These Aluminum Terminals Have The Same Design Features And Benefits As The 1-Hole Ya-A , With An Added Stud Hole For A More Secure Termination To Various Types Of Equipment Pads, They Are Dual-Rated For Use On Both Aluminum And Copper Conductors, Tools, Die Set Catalog Number, And (number Of Crimps): Y35, Y39, Y750, Y4

Manufacturer Information

Brand	BURNDY
GTIN	00781810753118
Manufacturers Part Number	YA25A7
UPC	781810753118



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	YA-A

Packaging

Carton	1
Package	10
Weight Per each	0.09

Uses, Certifications, and Standards

Application	Wire Termination
standard	UL 486A-486B