



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



TY23M 3.62" Ty-Rap (Bulk)

Abb Installation Products, Inc

Catalog Number	TY23M
Manufacturer	Abb Installation Products, Inc
Description	Cable Tie, Natural Polyamide (Nylon 6.6) For Temperatures Up to 85 Degrees Celsius (185 F) For Indoor Applications, UI/En/CSA62275 Type 2/21 Rated For Ah-2 Plenum, Length Of 92MM (3.6 Inches), Width Of 2.3MM (0.09 Inches), Thickness Of 1MM (0.04 Inch), Tensile Strength Rating Of 80 Newtons (18 Pounds), Bulk Pack
Weight per unit	0.0010 (lbs/each)
Product Category	Cable Ties & Wraps

Features

Tensile Strength	18
------------------	----

Dimensions and Weight

Length	3.6
Thickness	0.04
Width	0.09

Descriptions

Description	3.62" TY-RAP (BULK)
extra long description	ABB TY23M CABLE TIE 18LB 4IN NATURA
Long Description	Cable Tie, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, UL/EN/CSA62275 Type 2/21 Rated for AH-2 Plenum, Length of 92mm (3.6 Inches), Width of 2.3mm (0.09 Inches), Thickness of 1mm (0.04 Inch), Tensile Strength Rating of 80 Newtons (18 Pounds), Bulk Pack
Product Type	Cable Tie 18LB 4IN Natural Nylon
Special Features	Low profile head is designed to prevent snags on uneven surfaces and easier to pull through bulkheads. Non-magnetic stainless steel locking device insures both maximum strength and the right tightness every time

Manufacturer Information

Brand	Ty-Rap
GTIN	00786210824369
Manufacturers Part Number	TY23M
UPC	786210824369



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Screws, Bolts, Staples, Jack Chains, Washers & TY-Raps
Type	HIGH PERFORMANCE

Availability

minimum qty	1000
-------------	------

Packaging

Carton	1000
Weight Per each	0.001

Uses, Certifications, and Standards

standard	UL E49405
----------	-----------