



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



TY525MCLRS Multclr Nyl CBL Tie

Abb Installation Products, Inc

Catalog Number	TY525MCLRS
Manufacturer	Abb Installation Products, Inc
Description	High Performance Cable Tie, Multiple Color Pack (Nylon 6.6) For Temperatures Up to 85 Degrees Celsius (185 F) For Indoor Applications, Length Of 183MM (7.2 Inches), Width Of 4.8MM (0.19 Inch), Tensile Strength Rating Of 222 Newtons (50 Pounds), 100 Pack Of 10 (Each) Standard Colors
Weight per unit	0.0040 (lbs/each)
Product Category	Cable Ties & Wraps

Features

Tensile Strength	50
------------------	----

Dimensions and Weight

Length	7.2
Thickness	0.05
Width	0.19

Descriptions

Description	MULTCLR NYL CBL TIE
extra long description	ABB TY525M-CLRS CABLE TIE 50LB 7IN
Long Description	High Performance Cable Tie, Multiple Color Pack (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, Length of 183mm (7.2 Inches), Width of 4.8mm (0.19 Inch), Tensile Strength Rating of 222 Newtons (50 Pounds), 100 Pack of 10 (Each) Standard Colors
Product Type	Cable Tie 50LB 7IN PK Multi-Colors
Special Features	Low profile head is designed to prevent snags on uneven surfaces and easier to pull through bulkheads. Non-magnetic stainless steel locking device insures both maximum strength and the right tightness every time

Manufacturer Information

Brand	Ty-Fast
GTIN	00786210932453
Manufacturers Part Number	TY525M-CLRS
UPC	786210932453

Taxonomies, Classifications, and Categories

Category Description	Screws, Bolts, Staples, Jack Chains, Washers & TY-Raps
Type	HIGH PERFORMANCE



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Availability

minimum qty 100

Packaging

Carton 100

Package 1000

Weight Per package 0.004

Uses, Certifications, and Standards

standard UL E49405