ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
5617 Andrews Hwy
Odessa, TX 79762-0000
Phone: 4323660008
Fax: 4323666045



U217MTBP 100A 7T RT OU MAIN

MILBANK

Catalog Number	U217MTBP
Manufacturer	MILBANK
Description	7 TERM RNGTP SML CLS PLT LNK BYPS 1-100 AMP MN PULLOUT
Weight per unit	40.0 (lbs/each)
Product Category	Test Block Bypass Meter Socket

Features

Bypass Type	Link Bypass
Cable Entry	Overhead or Underground
Phase	3 Phase
Voltage Rating	Up to 240 Volts Alternating Current
Amperage Rating	100 Continuous Ampere
Cutout Size	One 100 Ampere Main Fuse Pull Out Switch
Insulation	Fiberglass with Resin

Dimensions and Weight

Size	4.567L x 18.125W x 24.75H

Descriptions

Also Known As...	Meter Socket
	Meter Box
Description	100A 7T RT OU MAIN
Long Description	7 TERM RNGTP SML CLS PLT LNK BYPS 1-100 AMP MN PULLOUT
Product Type	100A 7T RT Ou Main 13498
Extra Long Description	MILB U217MTB-P 100A 7T RT OU MAIN 1

Manufacturer Information

Brand	MILBANK
GTIN	00784572134980
Manufacturers Part Number	U217MTB-P
UPC	785972

Taxonomies, Classifications, and Categories

Category Description	Meter Sockets
Type	Ring Type Meter Socket

Packaging

Carton	1
Weight Per Each	40.0 (lbs/each)


ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
5617 Andrews Hwy
Odessa, TX 79762-0000
Phone: 4323660008
Fax: 4323666045

Uses, Certifications, and Standards

Application	Meter Socket With Main
Enclosure	G90 Galvanized Steel with Powder Coat Finish
Frequency Rating	60 Hertz
Mounting	Surface Mount
Standard	UL Listed;Type 3R

MILBANK®
ENERGY AT WORK

U217MTB-P





Catalog Number	U217MTB-P
Marketing Product Description	7 Terminal Ring Type Small Closing Plate Test Block Bypass 1-100 Ampere Main Pullout
UPC	784572134980
Length (IN)	4.567
Width (IN)	18.125
Height (IN)	24.75
Brand Name	Milbank
Type	Ring Type Meter Socket
Application	Meter Socket With Main
Standard	UL Listed;Type 3R
Voltage Rating	Up to 240 Volts Alternating Current
Amperage Rating	100 Continuous Ampere
Phase	3 Phase
Frequency Rating	60 Hertz
Size	4.567L x 18.125W x 24.75H
Number Of Cutouts	1
Cutout Size	One 100 Ampere Main Fuse Pull Out Switch
Cable Entry	Overhead or Underground
Terminal	Single Mechanical
Insulation	Fiberglass with Resin


Mounting	Surface Mount
Enclosure	G90 Galvanized Steel with Powder Coat Finish
Jaw Quantity	7 Terminal
Bypass Type	Test Block Bypass
Number of Meter Positions	1 Position
Equipment Ground	Ground Lug
Hub Opening	Twin Small Closing Plates
Line Side Wire Range	14 AWG - 1/0
Load Side Wire Range	14 - 1/0 AWG
Number Of Receptacles	0


Please consult serving utility for their requirements prior to ordering or installing, as specifications and approvals vary by utility and may require local electrical inspector approval. All installations must be installed by a licensed electrician and must comply with all national and local codes, laws and regulations. Milbank reserves the right to make changes in specifications and features shown without notice or obligation.

FEATURE TABLE		
ITEM	QTY	DESCRIPTION
A	4	STD. MNTG. EMBOSS
B	2	½, ¾ CONC. K.O.
C	3	1¼, 1½ CONC. K.O.
D	2	1¼, 1½, 2 CONC. K.O.
E	1	1¼, 1½, 2, 2½ CONC. K.O.









MILBANK®
ENERGY AT WORK

Version:

1

All dimensions are +/- 1/16".
Drawing views are not to scale.

Please consult serving utility for their requirements prior to ordering or installing, as specifications and approvals vary by utility, and may require local electrical inspector approval. All installations must be installed by a licensed electrician and must comply with all national and local codes, laws and regulations. Milbank reserves the right to make changes in specifications and features shown without notice or obligation.