




MILBANK
ENERGY AT WORK

U5934-XL-BLG




Catalog Number	U5934-XL-BLG	Enclosure	G90 Galvanized Steel with Powder Coat Finish
Marketing Product Description	4 Terminal Ringless Small Closing Plate 7-8 In Barrel Lock Ground With Bracket Provision	Jaw Quantity	4 Terminal
UPC	784572592278	Bypass Type	No Bypass
Length (IN)	3.61	Number of Meter Positions	1 Position
Width (IN)	8	Equipment Ground	Ground Bar
Height (IN)	11.5	Hub Opening	Small Closing Plate
Brand Name	Milbank	Line Side Wire Range	12 - 1/0 AWG
Type	Ringless Meter Socket	Load Side Wire Range	12 - 1/0 AWG
Application	Meter Socket	Number Of Receptacles	0
Standard	UL Listed;Type 3R		
Voltage Rating	600 Volts Alternating Current		
Amperage Rating	100 Continuous Ampere		
Phase	1 Phase		
Frequency Rating	60 Hertz		
Size	3.61L x 8W x 11.5H		
Number Of Cutouts	0		
Cutout Size	No Main Breaker		
Cable Entry	Overhead or Underground		
Terminal	Single Mechanical		
Insulation	Glass Polyester		
Mounting	Surface Mount		

Please consult serving utility for their requirements prior to ordering or installing, as specifications and approvals vary by utility and may require local electrical inspector approval. All installations must be installed by a licensed electrician and must comply with all national and local codes, laws and regulations. Milbank reserves the right to make changes in specifications and features shown without notice or obligation.



MILBANK[®]
ENERGY AT WORK

U5934-XL-BLG



Catalog Number	U5934-XL-BLG	Enclosure	G90 Galvanized Steel with Powder Coat Finish
Marketing Product Description	4 Terminal Ringless Small Closing Plate 7-8 In Barrel Lock Ground With Bracket Provision	Jaw Quantity	4 Terminal
UPC	784572592278	Bypass Type	No Bypass
Length (IN)	3.61	Number of Meter Positions	1 Position
Width (IN)	8	Equipment Ground	Ground Bar
Height (IN)	11.5	Hub Opening	Small Closing Plate
Brand Name	Milbank	Line Side Wire Range	12 - 1/0 AWG
Type	Ringless Meter Socket	Load Side Wire Range	12 - 1/0 AWG
Application	Meter Socket	Number Of Receptacles	0
Standard	UL Listed;Type 3R		
Voltage Rating	600 Volts Alternating Current		
Amperage Rating	100 Continuous Ampere		
Phase	1 Phase		
Frequency Rating	60 Hertz		
Size	3.61L x 8W x 11.5H		
Number Of Cutouts	0		
Cutout Size	No Main Breaker		
Cable Entry	Overhead or Underground		
Terminal	Single Mechanical		
Insulation	Glass Polyester		
Mounting	Surface Mount		

Please consult serving utility for their requirements prior to ordering or installing, as specifications and approvals vary by utility and may require local electrical inspector approval. All installations must be installed by a licensed electrician and must comply with all national and local codes, laws and regulations. Milbank reserves the right to make changes in specifications and features shown without notice or obligation.